



Anti-MOUSE SERUM (GOAT) Antibody - 110-1101

Code: 110-1101

Size: 2 mL

Product Description: Anti-MOUSE SERUM (GOAT) Antibody - 110-1101

Concentration: 85 mg/mL by Refractometry

PhysicalState: Lyophilized

Label	Unconjugated
Host	Goat
Species Reactivity	mouse
Buffer	0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2
Stabilizer	None
Preservative	0.01% (w/v) Sodium Azide
Storage Condition	Store vial at 4° C prior to restoration. For extended storage aliquot contents and freeze at -20° C or below. Avoid cycles of freezing and thawing. Centrifuge product if not completely clear after standing at room temperature. This product is stable for several weeks at 4° C as an undiluted liquid. Dilute only prior to immediate use.
Synonyms	Anti-mouse whole serum, anti-mouse serum, anti-serum, detect mouse serum proteins
Purity And Specificity	This product was prepared from polyspecific antiserum by a delipidation and defibrination. Assay by immunoelectrophoresis resulted in multiple precipitin arcs against Mouse Serum.
Assay Dilutions	User Optimized
ELISA	User Optimized
WESTERN BLOT	User Optimized
OTHER ASSAYS	User Optimized
Expiration	Expiration date is one (1) year from date of opening.
Immunogen	Mouse serum proteins

Related Products

110-4101	Anti-MOUSE SERUM (RABBIT) Antibody - 110-4101
205-3202	Anti-GOAT IgG (H&L) (MOUSE) Antibody Fluorescein Conjugated - 205-3202
205-4202	Anti-GOAT IgG (H&L) (RABBIT) Antibody Fluorescein Conjugated - 205-4202

Related Links

Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 5199, Limerick, Pennsylvania, USA.