



Group A Streptococcus Antibody (FITC)

CATALOG NUMBER: 35-194

Specifications

SPECIES REACTIVITY:	Bacteria
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Specific to type specific carbohydrate of group A Streptococcus
IMMUNOGEN:	Streptococci, group A
HOST SPECIES:	Goat

Properties

PURIFICATION:	Purified IgG fraction of antiserum covalently coupled with high purity Isomer I of fluorescein isothiocyanate. Care is taken to insure complete removal of any free fluorescein from the final product.
PHYSICAL STATE:	Liquid
BUFFER:	Group A Streptococcus antibody is in a phosphate saline buffer (0.01M, pH 7.2) containing bovine serum albumin (10 mg/ml) as a stabilizer and 0.1% sodium azide preservative.
STORAGE CONDITIONS:	Group A Streptococcus antibody can be stored at -20°C, stable for one year.
CLONALITY:	Polyclonal
CONJUGATE:	FITC

Additional Info

ALTERNATE NAMES:	Anti-Group A Streptococcus Fluorescein conjugate
-------------------------	--

Background

FOR RESEARCH USE ONLY

December 12, 2016