




HMGB1 Antibody [1D5]

CATALOG NUMBER: 51-465



Immunohistochemistry of human placenta tissue stained using HMGB1 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	HMGB1 antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	HMGB1 (AAH03378, 1 a.a. ~ 216 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Store HMGB1 antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HMGB1, Amphoterin, High mobility group protein B1, High mobility group box 1, High mobility group protein 1, HMG1, HMG3, SBP-1, High-mobility group box 1, HMG-1
ACCESSION NO.:	P09429
PROTEIN GI NO.:	123369
OFFICIAL SYMBOL:	HMGB1
GENE ID:	3146

FOR RESEARCH USE ONLY

December 13, 2016