




WDR77 Antibody [3F10]

CATALOG NUMBER: 51-611



Immunoperoxidase of monoclonal antibody to WDR77 on formalin-fixed paraffin-embedded human tonsil (antibody concentration 3 ug/mL).

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	WDR77 antibody can be used in Western Blot, immunohistochemistry starting at 1:50, and immunoprecipitation.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	WDR77 (AAH01679, 1 a.a. ~ 343 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Store WDR77 antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	WDR77, Androgen receptor cofactor p44, HKMT1069, MEP-50, Methylosome protein 50, p44, MEP50, Nbla10071, RP11-552M11.3, WD repeat domain 77
ACCESSION NO.:	Q9BQA1
PROTEIN GI NO.:	32171507
OFFICIAL SYMBOL:	WDR77
GENE ID:	79084

FOR RESEARCH USE ONLY

December 13, 2016