




BIK Antibody [4G12]

CATALOG NUMBER: 51-888



Immunohistochemistry of human tonsil tissue stained using BIK Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	BIK antibody can be used in Western Blot starting at 2 ug/mL, and immunohistochemistry starting at 1:50.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	BIK (AAH01599, 37 a.a. ~ 136 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Aliquot and store BIK antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	BIK, Apoptosis inducer NBK, Bcl-2-interacting killer, BP4, Apoptosis-inducing NBK, BIP1, NBK
ACCESSION NO.:	Q13323
PROTEIN GI NO.:	2493284
OFFICIAL SYMBOL:	BIK
GENE ID:	638

Background

