



CD40 Recombinant Protein

CATALOG NUMBER: 92-602

Specifications

SPECIES:	Mouse
SOURCE SPECIES:	Human Cells
SEQUENCE:	Leu20-Arg193
FUSION TAG:	C-Fc tag
APPLICATIONS:	This recombinant protein can be used for biological assays. For research use only.

Properties

PURITY:	Greater than 95% as determined by reducing SDS-PAGE. Endotoxin level less than 0.1 ng/ug (1 IEU/ug) as determined by LAL test.
PREDICTED MOLECULAR WEIGHT:	46.5 kD
PHYSICAL STATE:	Lyophilized
BUFFER:	Lyophilized from a 0.2 um filtered solution of PBS,pH7.4. It is not recommended to reconstitute to a concentration less than 100 ug/ml. Dissolve the lyophilized protein in ddH2O.
STORAGE CONDITIONS:	Lyophilized protein should be stored at -20°C, though stable at room temperature for 3 weeks. Reconstituted protein solution can be stored at 4-7°C for 2-7 days. Aliquots of reconstituted samples are stable at -20°C for 3 months.

Additional Info

ALTERNATE NAMES:	Tumor Necrosis Factor Receptor Superfamily member 5, B-Cell Surface Antigen CD40, Bp50, CD40L Receptor, CDw40, CD40, TNFRSF5
ACCESSION NO.:	P27512

Background

CD40 is a Type I Transmembrane Glycoprotein that belongs to the TNF Receptor Superfamily. CD40 is expressed in B cells, follicular dendritic cells, dendritic cells, activated monocytes, macrophages, endothelial cells, vascular smooth muscle cells, and several tumor cell lines. The extracellular domain of CD40 is characterized by Cysteine rich repeat regions. Interaction of CD40 with its ligand (CD40L) leads to aggregation of CD40 molecules, which in turn interact with cytoplasmic components to initiate signaling pathways. Several different TRAF proteins (adaptor proteins) have been identified to serves as mediators of the signal transduction. CD40 plays an essential role in mediating a broad variety of immune and inflammatory responses including T cell-dependent immunoglobulin class switching, memory B cell development, and germinal center formation.

FOR RESEARCH USE ONLY

December 14, 2016