



Cadherin-1 Recombinant Protein

CATALOG NUMBER: 92-676

Specifications

SPECIES:	Human
SOURCE SPECIES:	Human Cells
SEQUENCE:	Asp155-Ile707
FUSION TAG:	C-6 His tag
APPLICATIONS:	This recombinant protein can be used for biological assays. For research use only.

Properties

PURITY:	Greater than 95% as determined by reducing SDS-PAGE. Endotoxin level less than 0.1 ng/ug (1 IEU/ug) as determined by LAL test.
PREDICTED MOLECULAR WEIGHT:	61.2 kD
PHYSICAL STATE:	Lyophilized
BUFFER:	Lyophilized from a 0.2 um filtered solution of PBS, pH 7.4. It is not recommended to reconstitute to a concentration less than 100 ug/ml. Dissolve the lyophilized protein in ddH ₂ O.
STORAGE CONDITIONS:	Lyophilized protein should be stored at -20°C, though stable at room temperature for 3 weeks. Reconstituted protein solution can be stored at 4-7°C for 2-7 days. Aliquots of reconstituted samples are stable at -20°C for 3 months.

Additional Info

ALTERNATE NAMES:	Cadherin-1, CDH1, CAM 120/80, E-cadherin, CD324
ACCESSION NO.:	P12830

Background

E-Cadherin is a classical member of the cadherin superfamily. The encoded protein is a calcium-dependent cell-cell adhesion glycoprotein composed of five extracellular cadherin repeats, a transmembrane region, and a highly conserved cytoplasmic tail. Mutations in this gene are correlated with gastric, breast, colorectal, thyroid, and ovarian cancers. Loss of function is thought to contribute to progression in cancer by increasing proliferation, invasion, and/or metastasis. The ectodomain of this protein mediates bacterial adhesion to mammalian cells, and the cytoplasmic domain is required for internalization. Identified transcript variants arise from mutation at consensus splice sites. Also, E-Cadherin has a potent invasive suppressor role and it is a ligand for integrin alpha-E/beta-7.

FOR RESEARCH USE ONLY

December 14, 2016