



## Anti-MOUSE Red Blood Cell (RBC) (RABBIT) Antibody - 110-4139

**Code:** 110-4139

**Size:** 2 mL

**Product Description:** Anti-MOUSE Red Blood Cell (RBC) (RABBIT) Antibody - 110-4139

**Concentration:** 65 mg/mL by Refractometry

**PhysicalState:** Lyophilized

<b>Label</b>	Unconjugated
<b>Host</b>	Rabbit
<b>Buffer</b>	0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2
<b>Reconstitution Volume</b>	2.0 mL
<b>Reconstitution Buffer</b>	Restore with deionized water (or equivalent)
<b>Stabilizer</b>	None
<b>Preservative</b>	0.01% (w/v) Sodium Azide
<b>Storage Condition</b>	Store vial at 4° C prior to restoration. For extended storage aliquot contents and freeze at -20° C or below. Avoid cycles of freezing and thawing. Centrifuge product if not completely clear after standing at room temperature. This product is stable for several weeks at 4° C as an undiluted liquid. Dilute only prior to immediate use.
<b>Synonyms</b>	Anti-RBC antibody, Red blood cell antibody, Antibody for hemagglutination, rabbit anti RBC, rabbit antibody to mouse red blood cells (RBC), haemolysin, hemolysin, erythrocytes sensitizing agent, anti-erythrocytes, anti-erythrocytes antibody
<b>Purity And Specificity</b>	This product was prepared from polyspecific antiserum by a delipidation and defibrination.
<b>Assay Dilutions</b>	AGGLUTINATION TITER 1:32 - 1:64
<b>OTHER ASSAYS</b>	AGGLUTINATION TITER 1:32 - 1:64
<b>Expiration</b>	Expiration date is one (1) year from date of opening.
<b>Immunogen</b>	Mouse washed pooled Red Blood Cells (RBC)
<b>Related Products</b>	

611-1302	Anti-RABBIT IgG (H&L) (GOAT) Antibody Peroxidase Conjugated - 611-1302
B304	NORMAL GOAT SERUM (NGS) - B304
C200-0005	GUINEA PIG COMPLEMENT (lyophilized) with DILUENT - C200-0005
R302-0050	CHICKEN BLOOD in Alsevers - R302-0050

### Related Links

### Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 5199, Limerick, Pennsylvania, USA.