

## SAFETY DATA SHEET

Creation Date 10-Feb-2011

Revision Date 23-May-2017

Revision Number 4

### 1. Identification

**Product Name** Phenylacetic acid hydrazide

**Cat No. :** AC130290000; AC130290250; AC130291000

**Synonyms** Benzeneacetic Acid, Hydrazide.

**Recommended Use** Laboratory chemicals.

**Uses advised against** Not for food, drug, pesticide or biocidal product use

#### Details of the supplier of the safety data sheet

##### Company

Fisher Scientific  
One Reagent Lane  
Fair Lawn, NJ 07410  
Tel: (201) 796-7100

Acros Organics  
One Reagent Lane  
Fair Lawn, NJ 07410

##### **Emergency Telephone Number**

For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11

Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99

**CHEMTREC** Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

### 2. Hazard(s) identification

#### Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute oral toxicity	Category 3
Skin Corrosion/irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3
Target Organs - Respiratory system.	

#### Label Elements

##### **Signal Word**

Danger

##### **Hazard Statements**

Toxic if swallowed  
Causes skin irritation  
Causes serious eye irritation  
May cause respiratory irritation

**Precautionary Statements****Prevention**

Wash face, hands and any exposed skin thoroughly after handling  
Do not eat, drink or smoke when using this product  
Wear protective gloves/protective clothing/eye protection/face protection  
Avoid breathing dust/fume/gas/mist/vapors/spray  
Use only outdoors or in a well-ventilated area

**Inhalation**

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
Call a POISON CENTER or doctor/physician if you feel unwell

**Skin**

IF ON SKIN: Wash with plenty of soap and water  
If skin irritation occurs: Get medical advice/attention  
Take off contaminated clothing and wash before reuse

**Eyes**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
If eye irritation persists: Get medical advice/attention

**Ingestion**

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician  
Rinse mouth

**Storage**

Store locked up  
Store in a well-ventilated place. Keep container tightly closed

**Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

None identified

### 3. Composition / information on ingredients

Component	CAS-No	Weight %
Benzeneacetic acid, hydrazide	937-39-3	>95

### 4. First-aid measures

**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Move to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

<b>Ingestion</b>	Do not induce vomiting. Call a physician or Poison Control Center immediately.
<b>Most important symptoms/effects</b>	None reasonably foreseeable.
<b>Notes to Physician</b>	Treat symptomatically

## 5. Fire-fighting measures

**Suitable Extinguishing Media** Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

**Unsuitable Extinguishing Media** No information available

**Flash Point** No information available  
**Method -** No information available

### Autoignition Temperature

### Explosion Limits

**Upper** No data available  
**Lower** No data available  
**Sensitivity to Mechanical Impact** No information available  
**Sensitivity to Static Discharge** No information available

### Specific Hazards Arising from the Chemical

Keep product and empty container away from heat and sources of ignition.

### Hazardous Combustion Products

Thermal decomposition can lead to release of irritating gases and vapors

### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

### NFPA

**Health**  
2

**Flammability**  
1

**Instability**  
0

**Physical hazards**  
N/A

## 6. Accidental release measures

**Personal Precautions** Ensure adequate ventilation. Use personal protective equipment. Avoid dust formation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

**Environmental Precautions** Should not be released into the environment.

**Methods for Containment and Clean Up** Sweep up or vacuum up spillage and collect in suitable container for disposal. Avoid dust formation.

## 7. Handling and storage

**Handling** Wear personal protective equipment. Do not get in eyes, on skin, or on clothing. Avoid dust formation. Use only under a chemical fume hood. Do not breathe vapors/dust. Do not ingest.

**Storage** Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

## 8. Exposure controls / personal protection

**Exposure Guidelines** This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

**Engineering Measures** Ventilation systems. Ensure that eyewash stations and safety showers are close to the workstation location.

**Personal Protective Equipment**

<b>Eye/face Protection</b>	Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.
<b>Skin and body protection</b>	Long sleeved clothing.
<b>Respiratory Protection</b>	Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.

**9. Physical and chemical properties**

<b>Physical State</b>	Solid
<b>Appearance</b>	White
<b>Odor</b>	No information available
<b>Odor Threshold</b>	No information available
<b>pH</b>	No information available
<b>Melting Point/Range</b>	115 - 117 °C / 239 - 242.6 °F
<b>Boiling Point/Range</b>	No information available
<b>Flash Point</b>	No information available
<b>Evaporation Rate</b>	Not applicable
<b>Flammability (solid,gas)</b>	No information available
<b>Flammability or explosive limits</b>	
Upper	No data available
Lower	No data available
<b>Vapor Pressure</b>	No information available
<b>Vapor Density</b>	Not applicable
<b>Specific Gravity</b>	No information available
<b>Solubility</b>	No information available
<b>Partition coefficient; n-octanol/water</b>	No data available
<b>Autoignition Temperature</b>	
<b>Decomposition Temperature</b>	No information available
<b>Viscosity</b>	Not applicable
<b>Molecular Formula</b>	C8 H10 N2 O
<b>Molecular Weight</b>	150.18

**10. Stability and reactivity**

<b>Reactive Hazard</b>	None known, based on information available
<b>Stability</b>	No information available.
<b>Conditions to Avoid</b>	Incompatible products.
<b>Incompatible Materials</b>	Strong oxidizing agents, Strong bases
<b>Hazardous Decomposition Products</b>	Thermal decomposition can lead to release of irritating gases and vapors
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Hazardous Reactions</b>	None under normal processing.

**11. Toxicological information****Acute Toxicity****Product Information**

**Component Information****Toxicologically Synergistic** No information available**Products****Delayed and immediate effects as well as chronic effects from short and long-term exposure****Irritation** Irritating to eyes and skin**Sensitization** No information available**Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Benzeneacetic acid, hydrazide	937-39-3	Not listed	Not listed	Not listed	Not listed	Not listed

**Mutagenic Effects** No information available**Reproductive Effects** No information available.**Developmental Effects** No information available.**Teratogenicity** No information available.**STOT - single exposure** Respiratory system**STOT - repeated exposure** None known**Aspiration hazard** No information available**Symptoms / effects, both acute and delayed** No information available**Endocrine Disruptor Information** No information available**Other Adverse Effects** The toxicological properties have not been fully investigated.

## 12. Ecological information

**Ecotoxicity**

Do not empty into drains.

**Persistence and Degradability** No information available**Bioaccumulation/ Accumulation** No information available.**Mobility** No information available.

## 13. Disposal considerations

**Waste Disposal Methods** Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

## 14. Transport information

**DOT**

**UN-No** UN2811  
**Proper Shipping Name** Toxic solid, organic, n.o.s  
**Proper technical name** Benzeneacetic acid, hydrazide  
**Hazard Class** 6.1  
**Packing Group** III

**TDG**

**UN-No** UN2811  
**Proper Shipping Name** TOXIC SOLID, ORGANIC, N.O.S.

<b>Hazard Class</b>	6.1
<b>Packing Group</b>	III
<b>IATA</b>	
<b>UN-No</b>	UN2811
<b>Proper Shipping Name</b>	TOXIC SOLID, ORGANIC, N.O.S.
<b>Hazard Class</b>	6.1
<b>Packing Group</b>	III
<b>IMDG/IMO</b>	
<b>UN-No</b>	UN2811
<b>Proper Shipping Name</b>	TOXIC SOLID, ORGANIC, N.O.S.
<b>Hazard Class</b>	6.1
<b>Packing Group</b>	III

## 15. Regulatory information

All of the components in the product are on the following Inventory lists: X = listed

### International Inventories

Component	TSCA	DSL	NDSL	EINECS	ELINCS	NLP	PICCS	ENCS	AICS	IECSC	KECL
Benzeneacetic acid, hydrazide	X	-	X	213-328-6	-		X	-	-	-	-

#### Legend:

X - Listed

E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.

F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.

N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.

P - Indicates a commenced PMN substance

R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.

S - Indicates a substance that is identified in a proposed or final Significant New Use Rule

T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.

XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B)).

Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.

Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

### U.S. Federal Regulations

**TSCA 12(b)** Not applicable

**SARA 313** Not applicable

#### SARA 311/312 Hazard Categories

<b>Acute Health Hazard</b>	Yes
<b>Chronic Health Hazard</b>	No
<b>Fire Hazard</b>	No
<b>Sudden Release of Pressure Hazard</b>	No
<b>Reactive Hazard</b>	No

**CWA (Clean Water Act)** Not applicable

**Clean Air Act** Not applicable

**OSHA Occupational Safety and Health Administration**  
Not applicable

**CERCLA**  
Not applicable

**California Proposition 65** This product does not contain any Proposition 65 chemicals

**U.S. State Right-to-Know Regulations** Not applicable

**U.S. Department of Transportation**

Reportable Quantity (RQ): N  
DOT Marine Pollutant N  
DOT Severe Marine Pollutant N

**U.S. Department of Homeland Security**

This product does not contain any DHS chemicals.

**Other International Regulations**

**Mexico - Grade** No information available

## 16. Other information

**Prepared By** Regulatory Affairs  
Thermo Fisher Scientific  
Email: EMSDS.RA@thermofisher.com

**Creation Date** 10-Feb-2011  
**Revision Date** 23-May-2017  
**Print Date** 23-May-2017  
**Revision Summary** SDS sections updated. 2. 11. 14. 15.

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**