



## Anti-MOUSE IgA (RABBIT) Antibody Alkaline Phosphatase Conjugated - 610-4506

**Code:** 610-4506

**Size:** 1 mg

**Product Description:** Anti-MOUSE IgA (RABBIT) Antibody Alkaline Phosphatase Conjugated - 610-4506

**Concentration:** 1.0 mg/mL by UV absorbance at 280 nm

**PhysicalState:** Liquid (sterile filtered)

<b>Label</b>	Alkaline Phosphatase (Calf Intestine)
<b>Host</b>	Rabbit
<b>Buffer</b>	0.05 M Tris Chloride, 0.15M Sodium Chloride, 0.001M Magnesium Chloride, 0.0001M Zinc Chloride, 50% (v/v) Glycerol; pH 8.0
<b>Stabilizer</b>	10 mg/mL Bovine Serum Albumin (BSA) - Immunoglobulin and Protease free
<b>Preservative</b>	0.01% (w/v) Sodium Azide
<b>Storage Condition</b>	Store vial at 4° C before opening. DO NOT FREEZE. This product is stable at 4° C as an undiluted liquid. Dilute only prior to immediate use. Freezing alkaline phosphatase conjugates will result in a substantial loss of enzymatic activity.
<b>Synonyms</b>	ALP, Alk Phos, Rabbit Anti-Mouse IgA Antibody, Rb-a-Mouse IgA, Mouse IgA Secondary Antibody
<b>Application Note</b>	Anti-MOUSE IgA (alpha chain) (RABBIT) Antibody is suitable for immunoblotting (western or dot blot), ELISA, immunoperoxidase electron microscopy and immunohistochemistry as well as other peroxidase-antibody based enzymatic assays requiring lot-to-lot consistency. Specific conditions should be optimized by user.
<b>Background</b>	MOUSE IgA (alpha chain) (RABBIT) Antibody generated in sheep detects specifically mouse IgA whole molecule. Anti-Mouse IgA antibody is ideal for investigators who routinely perform ELISA, Sandwich ELISA, titration assays, western-blot, immunoprecipitation and more generally immunoassays.
<b>Purity And Specificity</b>	Anti-MOUSE IgA (alpha chain) (RABBIT) Antibody was prepared from monospecific antiserum by immunoaffinity chromatography using antigens coupled to agarose beads followed by solid phase adsorption(s) to remove any unwanted reactivities. Assay by immunoelectrophoresis resulted in a single precipitin arc against anti-Alkaline Phosphatase (calf intestine), anti-Rabbit Serum, Mouse IgA and Mouse Serum. Specificity was confirmed by ELISA against other mouse heavy or light chain isotypes.
<b>Assay Dilutions</b>	User Optimized
<b>ELISA</b>	1:1,000 - 1:8,000
<b>Immunohistochemistry</b>	1:100 - 1:500
<b>WESTERN BLOT</b>	1:100 - 1:1,000
<b>IHC</b>	1:100 - 1:500
<b>OTHER ASSAYS</b>	User Optimized
<b>Immunogen</b>	Mouse IgA alpha heavy chain

### Related Products

610-4302	Anti-MOUSE IgG (H&L) (RABBIT) Antibody Peroxidase Conjugated - 610-4302
B501-0500	BLOTTO Immunoanalytical Grade (Non-Fat Dry Milk) - B501-0500
BSA-50	BOVINE SERUM ALBUMIN - Fraction V (Immunoglobulin and Protease Free) - BSA-50
MB-070	Blocking Buffer for Fluorescent Western Blotting - MB-070

### Related Links

### Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 5199, Limerick, Pennsylvania, USA.