

# SAFETY DATA SHEET

Revision Date 26-May-2017

Revision Number 2

## 1. Identification

**Product Name** L-Aspartic acid dimethyl ester hydrochloride**Cat No. :** AC376660000; AC376660050; AC376660250**Synonyms** No information available**Recommended Use** Laboratory chemicals.**Uses advised against** Not for food, drug, pesticide or biocidal product use

### Details of the supplier of the safety data sheet

**Company**Fisher Scientific  
One Reagent Lane  
Fair Lawn, NJ 07410  
Tel: (201) 796-7100Acros Organics  
One Reagent Lane  
Fair Lawn, NJ 07410**Emergency Telephone Number**For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99**CHEMTREC** Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

## 2. Hazard(s) identification

**Classification**

Classification under 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Based on available data, the classification criteria are not met

**Label Elements**

None required

**Hazards not otherwise classified (HNOC)**

None identified

## 3. Composition / information on ingredients

Component	CAS-No	Weight %
Dimethyl L-aspartate hydrochloride	32213-95-9	99

## 4. First-aid measures

**Eye Contact**Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.  
Obtain medical attention.

<b>Skin Contact</b>	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Obtain medical attention.
<b>Inhalation</b>	Remove from exposure, lie down. Move to fresh air.
<b>Ingestion</b>	Clean mouth with water. Get medical attention.
<b>Most important symptoms/effects Notes to Physician</b>	No information available. Treat symptomatically

## 5. Fire-fighting measures

<b>Suitable Extinguishing Media</b>	Water spray. Carbon dioxide (CO <sub>2</sub> ). Dry chemical. Chemical foam.
<b>Unsuitable Extinguishing Media</b>	No information available
<b>Flash Point</b>	No information available
<b>Method -</b>	No information available
<b>Autoignition Temperature</b>	No information available
<b>Explosion Limits</b>	
<b>Upper</b>	No data available
<b>Lower</b>	No data available
<b>Sensitivity to Mechanical Impact</b>	No information available
<b>Sensitivity to Static Discharge</b>	No information available

### Specific Hazards Arising from the Chemical

Keep product and empty container away from heat and sources of ignition.

### Hazardous Combustion Products

Hydrogen chloride gas Nitrogen oxides (NO<sub>x</sub>) Carbon monoxide (CO) Carbon dioxide (CO<sub>2</sub>)

### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### NFPA

**Health**  
0

**Flammability**  
0

**Instability**  
0

**Physical hazards**  
N/A

## 6. Accidental release measures

<b>Personal Precautions</b>	Ensure adequate ventilation. Use personal protective equipment.
<b>Environmental Precautions</b>	See Section 12 for additional ecological information.

**Methods for Containment and Clean Up** Sweep up or vacuum up spillage and collect in suitable container for disposal.

## 7. Handling and storage

<b>Handling</b>	Avoid contact with skin and eyes. Do not breathe dust. Do not breathe vapors or spray mist.
<b>Storage</b>	Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

## 8. Exposure controls / personal protection

<b>Exposure Guidelines</b>	This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.
----------------------------	---

<b>Engineering Measures</b>	Ensure adequate ventilation, especially in confined areas.
-----------------------------	--

**Personal Protective Equipment**

<b>Eye/face Protection</b>	Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.
<b>Skin and body protection</b>	Wear appropriate protective gloves and clothing to prevent skin exposure.
<b>Respiratory Protection</b>	Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.

**9. Physical and chemical properties**

<b>Physical State</b>	Powder Solid
<b>Appearance</b>	Off-white
<b>Odor</b>	No information available
<b>Odor Threshold</b>	No information available
<b>pH</b>	No information available
<b>Melting Point/Range</b>	115 - 117 °C / 239 - 242.6 °F
<b>Boiling Point/Range</b>	No information available
<b>Flash Point</b>	No information available
<b>Evaporation Rate</b>	No information available
<b>Flammability (solid,gas)</b>	No information available
<b>Flammability or explosive limits</b>	
Upper	No data available
Lower	No data available
<b>Vapor Pressure</b>	No information available
<b>Vapor Density</b>	No information available
<b>Specific Gravity</b>	No information available
<b>Solubility</b>	No information available
<b>Partition coefficient; n-octanol/water</b>	No data available
<b>Autoignition Temperature</b>	No information available
<b>Decomposition Temperature</b>	No information available
<b>Viscosity</b>	No information available
<b>Molecular Formula</b>	C6 H11 N O4 . H Cl
<b>Molecular Weight</b>	197.62

**10. Stability and reactivity**

<b>Reactive Hazard</b>	None known, based on information available
<b>Stability</b>	Stable under normal conditions.
<b>Conditions to Avoid</b>	Excess heat. Incompatible products.
<b>Incompatible Materials</b>	Strong oxidizing agents
<b>Hazardous Decomposition Products</b>	Hydrogen chloride gas, Nitrogen oxides (NOx), Carbon monoxide (CO), Carbon dioxide (CO <sub>2</sub> )
<b>Hazardous Polymerization</b>	No information available.
<b>Hazardous Reactions</b>	None under normal processing.

**11. Toxicological information****Acute Toxicity**

**Product Information** No acute toxicity information is available for this product

**Component Information**

**Toxicologically Synergistic** No information available

**Products**

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Irritation** No information available

**Sensitization** No information available

**Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Dimethyl L-aspartate hydrochloride	32213-95-9	Not listed	Not listed	Not listed	Not listed	Not listed

**Mutagenic Effects** No information available

**Reproductive Effects** No information available.

**Developmental Effects** No information available.

**Teratogenicity** No information available.

**STOT - single exposure** None known

**STOT - repeated exposure** None known

**Aspiration hazard** No information available

**Symptoms / effects, both acute and delayed** No information available

**Endocrine Disruptor Information** No information available

**Other Adverse Effects** The toxicological properties have not been fully investigated.

## 12. Ecological information

### Ecotoxicity

Do not empty into drains.

**Persistence and Degradability** No information available

**Bioaccumulation/ Accumulation** No information available.

**Mobility** No information available.

## 13. Disposal considerations

**Waste Disposal Methods** Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

## 14. Transport information

**DOT** Not regulated

**TDG** Not regulated

**IATA** Not regulated

**IMDG/IMO** Not regulated

## 15. Regulatory information

**International Inventories**

Component	TSCA	DSL	NDSL	EINECS	ELINCS	NLP	PICCS	ENCS	AICS	IECSC	KECL
Dimethyl L-aspartate hydrochloride	-	-	-	250-957-5	-		-	-	-	-	-

**Legend:**

X - Listed

E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.

F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.

N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.

P - Indicates a commenced PMN substance

R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.

S - Indicates a substance that is identified in a proposed or final Significant New Use Rule

T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.

XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B)).

Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.

Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

**U.S. Federal Regulations**

TSCA 12(b) Not applicable

SARA 313 Not applicable

**SARA 311/312 Hazard Categories**

Acute Health Hazard No

Chronic Health Hazard No

Fire Hazard No

Sudden Release of Pressure Hazard No

Reactive Hazard No

CWA (Clean Water Act) Not applicable

Clean Air Act Not applicable

OSHA Occupational Safety and Health Administration  
Not applicable**CERCLA**

Not applicable

California Proposition 65 This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations Not applicable

**U.S. Department of Transportation**

Reportable Quantity (RQ): N

DOT Marine Pollutant N

DOT Severe Marine Pollutant N

**U.S. Department of Homeland Security**

This product does not contain any DHS chemicals.

**Other International Regulations**

Mexico - Grade No information available

---

## 16. Other information

Prepared By	Regulatory Affairs Thermo Fisher Scientific Email: EMSDS.RA@thermofisher.com
Revision Date	26-May-2017
Print Date	26-May-2017
Revision Summary	This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**