

Printing date 01/11/2006

Reviewed on 05/13/2003

#### 1 Identification of substance:

· Product name: CDC Anaerobe Blood Agar

· Catalog number: 221734

· Manufacturer/Supplier:

BD Diagnostic Systems

7 Loveton Circle

Sparks, MD 21152

Tel: (410) 771-0100 or (800) 638-8663

· Information department: Technical Services

· Emergency information:

In case of a chemical emergency, spill, fire, exposure, or accident contact BD Diagnostic Systems at (410)771-0100 or (800)638-8663, or ChemTrec at (800)424-9300.

#### 2 Composition/Data on components:

- · Chemical characterization
- · Description: Mixture of the substances listed below with nonhazardous additions.
- · Dangerous components: Void

### 3 Hazards identification

· Hazard description:

This product contains no hazardous constituents, or the concentration of all chemical constituents are below the regulatory threshold limits described by Occupational Safety Health Administration Hazard Communication Standard 29 CFR 1910.1200 and the European Directive 91/155/EEC, and 93/112/EC.

- · Information pertaining to particular dangers for man and environment Not applicable
- · Classification system

The classification was made according to the latest editions of international substances lists, and expanded upon from company and literature data.

· NFPA ratings (scale 0-4)



Health = 0 Fire = 0Reactivity = 0

#### 4 First aid measures

- · General information No special measures required.
- · After inhalation Seek medical treatment in case of complaints.
- · After skin contact Immediately wash with water and soap and rinse thoroughly.
- · After eye contact

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

- · After swallowing If symptoms persist consult doctor.
- · Information for doctor Show this product label or this MSDS.

IIC A



Printing date 01/11/2006 Reviewed on 05/13/2003

Product name: CDC Anaerobe Blood Agar

(Contd. of page 1)

### 5 Fire fighting measures

· Suitable extinguishing agents

CO2, ABC multipurpose dry chemical or water spray. Fight larger fires with water spray or alcohol resistant foam.

· Protective equipment: No special measures required.

#### 6 Accidental release measures

- · Person-related safety precautions: Not required.
- · Measures for environmental protection: No special measures required.
- · Measures for cleaning/collecting: No special measures required.
- · Additional information: No dangerous substances are released.

### 7 Handling and storage

- · Handling
- · Information for safe handling: No special measures required.
- · Information about protection against explosions and fires: No special measures required.
- · Storage
- Requirements to be met by storerooms and receptacles: No special requirements.
- · Information about storage in one common storage facility: Not required.
- · Further information about storage conditions: None.

## 8 Exposure controls and personal protection

- · Additional information about design of technical systems: No further data; see item 7.
- · Components with limit values that require monitoring at the workplace:

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

- · Additional information: The lists that were valid during the creation were used as basis.
- · Personal Protective Equipment
- · General protective and hygienic measures

The usual precautionary measures for handling chemicals should be followed.

- · Breathing equipment: Not required.
- · Protection of hands:





Chemical resistant gloves (i.e. nitrile, or equivalent).

- · Eye protection: Safety glasses
- · **Body protection:** Protective work clothing (lab coat).

JSA



Printing date 01/11/2006 Reviewed on 05/13/2003

Product name: CDC Anaerobe Blood Agar

(Contd. of page 2)

General Information	
Form:	Liquid
Color:	Light beige
Odor:	Characteristic
Change in condition	
Melting point/Melting range:	Not determined
	Undetermined
Boiling point/Boiling range:	Not determined
	Undetermined
Flash point:	Not applicable
Auto igniting:	Product is not self igniting.
Danger of explosion:	Product does not present an explosion hazard.
Vapor pressure at 20°C (68°F):	23.0 mbar
Density:	Not determined
Solubility in / Miscibility with	
Water:	Soluble
Solvent content:	
Organic solvents:	0.0 %
Water:	72.4 %
· Solids content:	27.6 %

### 10 Stability and reactivity

- · Thermal decomposition / conditions to be avoided:
- No decomposition if used according to specifications.
- · Dangerous reactions No dangerous reactions known
- · Dangerous products of decomposition: No dangerous decomposition products known.

# 11 Toxicological information

- · Acute toxicity:
- · Primary irritant effect:
- · on the skin: No irritating effect.
- · on the eye: No irritating effect.
- · Sensitization: No sensitizing effects known.
- $\cdot \textit{Additional toxicological information:}$

The product is not subject to OSHA classification according to internally approved calculation methods for preparations.

When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

USA



Printing date 01/11/2006 Reviewed on 05/13/2003

Product name: CDC Anaerobe Blood Agar

(Contd. of page 3)

### 12 Ecological information:

- · Ecotoxical effects:
- · Other information:

The ecological effects have not been thoroughly investigated, but currently none have been identified.

· General notes: Generally not hazardous for water.

### 13 Disposal considerations

- · Product:
- · Recommendation

Smaller quantities can be disposed of with solid waste.

Dispose of material in accordance with federal (40 CFR 261.3), state and local requirements.

This product is not considered a RCRA hazardous waste.

- · Uncleaned packagings:
- · Recommendation: Disposal must be made according to state and federal regulations.
- · Recommended cleansing agent: Water, if necessary with cleansing agents.

#### 14 Transport information

- · DOT regulations:
- · Hazard class:
- · Land transport ADR/RID (cross-border)
- · ADR/RID class:
- · Maritime transport IMDG:
- · IMDG Class:
- · Marine pollutant: No
- · Air transport ICAO-TI and IATA-DGR:
- · ICAO/IATA Class: -
- · Transport/Additional information:

If a dashed line appears in the Hazard Class section for the type of transportation, this indicates the product is not regulated for transportation. However, if a Hazard Class Number is listed the product is regulated.

### 15 Regulations

· SARA Section 355 (extremely hazardous substances)

None of the ingredients is listed.

· SARA Section 313 (specific toxic chemical listings)

None of the ingredients is listed.

· TSCA (Toxic Substances Control Act)

9002-18-0 agar

8013-01-2 yeast extract

113-24-6 sodium pyruvate

(Contd. on page 5)



Printing date 01/11/2006 Reviewed on 05/13/2003

Product name: CDC Anaerobe Blood Agar

(Contd.	of:	nage	4
(Conta.	01	Puse	٠.

50-99-7	dextrose
	sodium carbonate
<i>56-89-3</i>	L-cystine

#### · California Proposition 65 - Chemicals known to cause cancer

None of the ingredients is listed.

· California Proposition 65 - Chemicals known to cause reproductive toxicity for females:

None of the ingredients is listed.

· California Proposition 65 - Chemicals known to cause reproductive toxicity for males:

None of the ingredients is listed.

· California Proposition 65 - Chemicals known to cause developmental toxicity:

None of the ingredients is listed.

- · Carcinogenicity categories
- · IARC (International Agency for Research on Cancer)

None of the ingredients is listed.

· NTP (National Toxicology Program)

None of the ingredients is listed.

· TLV (Threshold Limit Value established by ACGIH)

None of the ingredients is listed.

· Product related hazard information:

Observe the general safety regulations when handling chemicals

The product is not subject to identification regulations pertaining to regulations on hazardous materials.

- · National regulations
- · Water hazard class: Generally not hazardous for water.

#### 16 Other information:

To the best of our knowledge, the information contained herein is accurate. However, neither Becton, Dickinson and Company or any of its subsidiaries assumes any liabilities whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

- · Department issuing MSDS: Safety and Environment Department
- · Contact: Technical Service Representative

USA -