

## SAFETY DATA SHEET

Creation Date 26-Sep-2009

Revision Date 26-May-2017

Revision Number 3

### 1. Identification

**Product Name** Tris(hydroxymethyl)phosphine

**Cat No. :** AC363840000; AC363840010; AC363840250

**Synonyms** No information available

**Recommended Use** Laboratory chemicals.

**Uses advised against** Not for food, drug, pesticide or biocidal product use

#### Details of the supplier of the safety data sheet

##### Company

Fisher Scientific  
One Reagent Lane  
Fair Lawn, NJ 07410  
Tel: (201) 796-7100

Acros Organics  
One Reagent Lane  
Fair Lawn, NJ 07410

##### **Emergency Telephone Number**

For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11

Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99

**CHEMTREC** Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

### 2. Hazard(s) identification

#### Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute oral toxicity	Category 3
Skin Corrosion/irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 1
Specific target organ toxicity (single exposure)	Category 3
Target Organs - Respiratory system.	

#### Label Elements

##### **Signal Word**

Danger

##### **Hazard Statements**

Toxic if swallowed  
Causes skin irritation  
Causes serious eye damage  
May cause respiratory irritation

**Precautionary Statements****Prevention**

Wash face, hands and any exposed skin thoroughly after handling  
Do not eat, drink or smoke when using this product  
Wear protective gloves/protective clothing/eye protection/face protection  
Avoid breathing dust/fume/gas/mist/vapors/spray  
Use only outdoors or in a well-ventilated area

**Inhalation**

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
Call a POISON CENTER or doctor/physician if you feel unwell

**Skin**

IF ON SKIN: Wash with plenty of soap and water  
If skin irritation occurs: Get medical advice/attention  
Take off contaminated clothing and wash before reuse

**Eyes**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
Immediately call a POISON CENTER or doctor/physician

**Ingestion**

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician  
Rinse mouth

**Storage**

Store locked up  
Store in a well-ventilated place. Keep container tightly closed

**Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

None identified

### 3. Composition / information on ingredients

Component	CAS-No	Weight %
Methanol, phosphinidynetris-	2767-80-8	95

### 4. First-aid measures

**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Move to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

<b>Ingestion</b>	Do not induce vomiting. Call a physician or Poison Control Center immediately.
<b>Most important symptoms/effects</b>	None reasonably foreseeable. Causes severe eye damage.
<b>Notes to Physician</b>	Treat symptomatically

## 5. Fire-fighting measures

**Suitable Extinguishing Media** Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

**Unsuitable Extinguishing Media** No information available

**Flash Point** > 110 °C / > 230 °F

**Method -** No information available

**Autoignition Temperature**

**Explosion Limits**

**Upper** No data available

**Lower** No data available

**Sensitivity to Mechanical Impact** No information available

**Sensitivity to Static Discharge** No information available

**Specific Hazards Arising from the Chemical**

Keep product and empty container away from heat and sources of ignition.

**Hazardous Combustion Products**

Carbon monoxide (CO) Carbon dioxide (CO<sub>2</sub>) Oxides of phosphorus

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**NFPA**

**Health**  
3

**Flammability**  
1

**Instability**  
1

**Physical hazards**  
N/A

## 6. Accidental release measures

**Personal Precautions** Use personal protective equipment. Ensure adequate ventilation. Avoid dust formation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

**Environmental Precautions** Should not be released into the environment.

**Methods for Containment and Clean Up** Sweep up or vacuum up spillage and collect in suitable container for disposal. Avoid dust formation.

## 7. Handling and storage

**Handling** Wear personal protective equipment. Do not get in eyes, on skin, or on clothing. Avoid dust formation. Use only under a chemical fume hood. Do not breathe vapors/dust. Do not ingest.

**Storage** Keep container tightly closed in a dry and well-ventilated place. Store under an inert atmosphere.

## 8. Exposure controls / personal protection

**Exposure Guidelines** This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

**Engineering Measures** Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations

and safety showers are close to the workstation location.

#### **Personal Protective Equipment**

<b>Eye/face Protection</b>	Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.
<b>Skin and body protection</b>	Long sleeved clothing.
<b>Respiratory Protection</b>	Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.

### **9. Physical and chemical properties**

<b>Physical State</b>	Powder Solid
<b>Appearance</b>	White
<b>Odor</b>	No information available
<b>Odor Threshold</b>	No information available
<b>pH</b>	No information available
<b>Melting Point/Range</b>	48 - 56 °C / 118.4 - 132.8 °F
<b>Boiling Point/Range</b>	111 - 113 °C / 231.8 - 235.4 °F @ 2.5 mmHg
<b>Flash Point</b>	> 110 °C / > 230 °F
<b>Evaporation Rate</b>	Not applicable
<b>Flammability (solid,gas)</b>	No information available
<b>Flammability or explosive limits</b>	
Upper	No data available
Lower	No data available
<b>Vapor Pressure</b>	No information available
<b>Vapor Density</b>	Not applicable
<b>Specific Gravity</b>	No information available
<b>Solubility</b>	Soluble in water
<b>Partition coefficient; n-octanol/water</b>	No data available
<b>Autoignition Temperature</b>	
<b>Decomposition Temperature</b>	No information available
<b>Viscosity</b>	Not applicable
<b>Molecular Formula</b>	C3 H9 O3 P
<b>Molecular Weight</b>	124.08

### **10. Stability and reactivity**

<b>Reactive Hazard</b>	None known, based on information available
<b>Stability</b>	Hygroscopic. Air sensitive.
<b>Conditions to Avoid</b>	Incompatible products. Avoid dust formation. Exposure to moist air or water. Exposure to air.
<b>Incompatible Materials</b>	Halogens, oxygen, Strong oxidizing agents
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO), Carbon dioxide (CO <sub>2</sub> ), Oxides of phosphorus
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Hazardous Reactions</b>	None under normal processing.

### **11. Toxicological information**

**Acute Toxicity****Product Information  
Component Information**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Methanol, phosphinidynetris-	LD50 = 178 mg/kg ( Rat )	Not listed	Not listed

**Toxicologically Synergistic Products** No information available**Delayed and immediate effects as well as chronic effects from short and long-term exposure****Irritation** Causes severe eye burns Irritating to skin Irritating to respiratory system**Sensitization** No information available**Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Methanol, phosphinidynetris-	2767-80-8	Not listed	Not listed	Not listed	Not listed	Not listed

**Mutagenic Effects** No information available**Reproductive Effects** No information available.**Developmental Effects** No information available.**Teratogenicity** No information available.**STOT - single exposure** Respiratory system**STOT - repeated exposure** None known**Aspiration hazard** No information available**Symptoms / effects, both acute and delayed** No information available**Endocrine Disruptor Information** No information available**Other Adverse Effects** The toxicological properties have not been fully investigated.**12. Ecological information****Ecotoxicity**

Do not empty into drains.

**Persistence and Degradability** Soluble in water Persistence is unlikely based on information available.**Bioaccumulation/ Accumulation** No information available.**Mobility** Will likely be mobile in the environment due to its water solubility.**13. Disposal considerations****Waste Disposal Methods** Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.**14. Transport information****DOT**

UN-No	UN2811
Proper Shipping Name	Toxic solid, organic, n.o.s

Proper technical name	Methanol, phosphinidynetris-
Hazard Class	6.1
Packing Group	III
<b>TDG</b>	
UN-No	UN2811
Proper Shipping Name	TOXIC SOLID, ORGANIC, N.O.S.
Hazard Class	6.1
Packing Group	III
<b>IATA</b>	
UN-No	UN2811
Proper Shipping Name	TOXIC SOLID, ORGANIC, N.O.S.
Hazard Class	6.1
Packing Group	III
<b>IMDG/IMO</b>	
UN-No	UN2811
Proper Shipping Name	TOXIC SOLID, ORGANIC, N.O.S.
Hazard Class	6.1
Packing Group	III

## 15. Regulatory information

All of the components in the product are on the following Inventory lists: X = listed

### International Inventories

Component	TSCA	DSL	NDSL	EINECS	ELINCS	NLP	PICCS	ENCS	AICS	IECSC	KECL
Methanol, phosphinidynetris-	X	X	-	220-445-6	-		-	-	-	-	-

#### Legend:

X - Listed

E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.

F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.

N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.

P - Indicates a commenced PMN substance

R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.

S - Indicates a substance that is identified in a proposed or final Significant New Use Rule

T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.

XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B)).

Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.

Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

### U.S. Federal Regulations

TSCA 12(b) Not applicable

SARA 313 Not applicable

#### SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

CWA (Clean Water Act) Not applicable

Clean Air Act Not applicable

OSHA Occupational Safety and Health Administration  
Not applicable

**CERCLA**

Not applicable

**California Proposition 65**

This product does not contain any Proposition 65 chemicals

**U.S. State Right-to-Know Regulations**

Not applicable

**U.S. Department of Transportation**

Reportable Quantity (RQ):	N
DOT Marine Pollutant	N
DOT Severe Marine Pollutant	N

**U.S. Department of Homeland Security**

This product does not contain any DHS chemicals.

**Other International Regulations****Mexico - Grade**

No information available

**16. Other information****Prepared By**

Regulatory Affairs  
Thermo Fisher Scientific  
Email: EMSDS.RA@thermofisher.com

**Creation Date**

26-Sep-2009

**Revision Date**

26-May-2017

**Print Date**

26-May-2017

**Revision Summary**

This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**