SAFETY DATA SHEET

Creation Date 01-Sep-2009 **Revision Date** 26-May-2017 **Revision Number** 3

1. Identification

Product Name **Isopropanol**

Cat No. : **AC364400000; AC364400010; AC364400025; AC364401000**

Synonyms 2-Propanol; IPA; Isopropyl alcohol; Propan-2-ol; Isopropanol

Recommended Use Laboratory chemicals.
Uses advised against Not for food, drug, pesticide or biocidal product use

Details of the supplier of the safety data sheet

Company
Fisher Scientific
One Reagent Lane
Fair Lawn, NJ 07410
Tel: (201) 796-7100

Acros Organics
One Reagent Lane
Fair Lawn, NJ 07410

Emergency Telephone Number
For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11
Emergency Number **US:**001-201-796-7100 / **Europe:** +32 14 57 52 99
CHEMTREC Tel. No.**US:**001-800-424-9300 / **Europe:**001-703-527-3887

2. Hazard(s) identification

Classification
This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Flammable liquids	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3
Target Organs - Respiratory system, Central nervous system (CNS).	
Specific target organ toxicity - (repeated exposure)	Category 2
Target Organs - Kidney, Liver.	

Label Elements

Signal Word
Danger

Hazard Statements
Highly flammable liquid and vapor
Causes serious eye irritation
May cause respiratory irritation
May cause drowsiness or dizziness
May cause damage to organs through prolonged or repeated exposure



Precautionary Statements
Prevention
Wash face, hands and any exposed skin thoroughly after handling
Do not breathe dust/fume/gas/mist/vapors/spray
Use only outdoors or in a well-ventilated area
Keep away from heat/sparks/open flames/hot surfaces. - No smoking
Keep container tightly closed
Ground/bond container and receiving equipment
Use explosion-proof electrical/ventilating/lighting/equipment
Use only non-sparking tools
Take precautionary measures against static discharge
Wear protective gloves/protective clothing/eye protection/face protection
Keep cool
Response
Get medical attention/advice if you feel unwell
Inhalation
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
Call a POISON CENTER or doctor/physician if you feel unwell
Skin
IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower
Eyes
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention
Fire
In case of fire: Use CO2, dry chemical, or foam for extinction
Storage
Store in a well-ventilated place. Keep container tightly closed
Store locked up
Disposal
Dispose of contents/container to an approved waste disposal plant
Hazards not otherwise classified (HNOC)
None identified

3. Composition / information on ingredients

Component	CAS-No	Weight %
Isopropyl alcohol	67-63-0	>95

4. First-aid measures

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Obtain medical attention.

Skin Contact Wash off immediately with plenty of water for at least 15 minutes. Get medical attention if symptoms occur.

Inhalation Move to fresh air. Obtain medical attention. If not breathing, give artificial respiration.

Ingestion Do not induce vomiting. Obtain medical attention.

Most important symptoms/effects Breathing difficulties. May cause central nervous system depression: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

Notes to Physician Treat symptomatically

5. Fire-fighting measures

Suitable Extinguishing Media CO_2, dry chemical, dry sand, alcohol-resistant foam. Cool closed containers exposed to fire with water spray.

Unsuitable Extinguishing Media Water may be ineffective

Flash Point 12 °C / 53.6 °F

Method - Abel Closed Cup (BS 2000 Part 170, IP 170, AS/NZS 2106)

Autoignition Temperature 425 °C / 797 °F

Explosion Limits

Upper 12 vol %

Lower 2 vol %

Sensitivity to Mechanical Impact No information available

Sensitivity to Static Discharge No information available

Specific Hazards Arising from the Chemical

Flammable. Risk of ignition. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated.

Hazardous Combustion Products

Carbon monoxide (CO) Carbon dioxide (CO_2) peroxides

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

NFPA

Health	Flammability	Instability	Physical hazards
2	3	0	N/A

6. Accidental release measures

Personal Precautions Use personal protective equipment. Remove all sources of ignition. Take precautionary measures against static discharges. Avoid contact with skin, eyes and clothing.

Environmental Precautions Should not be released into the environment. See Section 12 for additional ecological information.

Methods for Containment and Clean Up Prevent further leakage or spillage if safe to do so. Remove all sources of ignition. Soak up with inert absorbent material. Take precautionary measures against static discharges. Use spark-proof tools and explosion-proof equipment. Keep in suitable, closed containers for disposal.

7. Handling and storage

Handling Wear personal protective equipment. Keep away from open flames, hot surfaces and sources of ignition. Use explosion-proof equipment. Use only non-sparking tools. Take precautionary measures against static discharges. Do not get in eyes, on skin, or on clothing. Do not breathe vapors or spray mist. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded.

Storage Keep away from heat and sources of ignition. Flammables area. Keep container tightly closed in a dry and well-ventilated place.

8. Exposure controls / personal protection

Exposure Guidelines

Component	ACGIH TLV	OSHA PEL	NIOSH IDLH	Mexico OEL (TWA)
Isopropyl alcohol	TWA: 200 ppm STEL: 400 ppm	(Vacated) TWA: 400 ppm (Vacated) TWA: 980 mg/m³ (Vacated) STEL: 500 ppm (Vacated) STEL: 1225 mg/m³ TWA: 400 ppm TWA: 980 mg/m³	IDLH: 2000 ppm TWA: 400 ppm TWA: 980 mg/m³ STEL: 500 ppm STEL: 1225 mg/m³	TWA: 400 ppm TWA: 980 mg/m³ STEL: 500 ppm STEL: 1225 mg/m³

Legend

ACGIH - American Conference of Governmental Industrial Hygienists
OSHA - Occupational Safety and Health Administration
NIOSH IDLH: The National Institute for Occupational Safety and Health Immediately Dangerous to Life or Health

Engineering Measures Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting/equipment. Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/face Protection Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure.

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Physical State	Liquid
Appearance	Colorless
Odor	Alcohol-like
Odor Threshold	No information available
pH	7 1% aq. sol
Melting Point/Range	-89.5 °C / -129.1 °F
Boiling Point/Range	81 - 83 °C / 177.8 - 181.4 °F @ 760 mmHg
Flash Point	12 °C / 53.6 °F
Method -	Abel Closed Cup (BS 2000 Part 170, IP 170, AS/NZS 2106)
Evaporation Rate	1.7
Flammability (solid,gas)	Not applicable
Flammability or explosive limits	
Upper	12 vol %
Lower	2 vol %
Vapor Pressure	43 mmHg @ 20 °C
Vapor Density	2.1 @ 20 °C / 68 °F
Specific Gravity	0.785
Solubility	Miscible with water
Partition coefficient; n-octanol/water	No data available
Autoignition Temperature	425 °C / 797 °F
Decomposition Temperature	No information available
Viscosity	2.27 mPa.s at 20 °C
Molecular Formula	C3 H8 O

Molecular Weight	60.1
VOC Content(%)	59.9 % (EC/1999/13)
Refractive index	1.377 at 20 °C / 68 °F (ASTM D-1218)
Surface tension	22.7 mN/m at 20 °C / 68 °F
Coefficient of expansion	0.0009 / °C
Dielectric constant	18.6 at 20 °C / 68 °F
Heat of vapourisation	665 J/g
Specific heat capacity	3 kJ/kg °C at 20 °C / 68 °F
Thermal conductivity	0.137 W/m °C at 20 °C / 68 °F

10. Stability and reactivity

Reactive Hazard None known, based on information available

Stability Stable under normal conditions.

Conditions to Avoid Heat, flames and sparks. Keep away from open flames, hot surfaces and sources of ignition.

Incompatible Materials Strong oxidizing agents, Acids, Halogens, Acid anhydrides

Hazardous Decomposition Products Carbon monoxide (CO), Carbon dioxide (CO_2), peroxides

Hazardous Polymerization Hazardous polymerization does not occur.

Hazardous Reactions None under normal processing.

11. Toxicological information

Acute Toxicity

Product Information

Component Information

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Isopropyl alcohol	5840 mg/kg (Rat)	13900 mg/kg (Rat) 12870 mg/kg (Rabbit)	72.6 mg/L (Rat) 4 h

Toxicologically Synergistic Products No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation Irritating to eyes and skin

Sensitization No information available

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Isopropyl alcohol	67-63-0	Not listed	Not listed	Not listed	Not listed	Not listed

Mutagenic Effects No information available

Reproductive Effects No information available.

Developmental Effects No information available.

Teratogenicity No information available.

STOT - single exposure Respiratory system Central nervous system (CNS)

STOT - repeated exposure Kidney Liver

Aspiration hazard No information available

Symptoms / effects,both acute and delayed May cause central nervous system depression: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

Endocrine Disruptor Information No information available

Other Adverse Effects The toxicological properties have not been fully investigated.

12. Ecological information

Ecotoxicity

. Do not empty into drains.

Component	Freshwater Algae	Freshwater Fish	Microtox	Water Flea
Isopropyl alcohol	EC50: > 1000 mg/L, 72h (Desmodesmus subspicatus) EC50: > 1000 mg/L, 96h (Desmodesmus subspicatus)	LC50: > 1400000 µg/L, 96h (Lepomis macrochirus) LC50: = 11130 mg/L, 96h static (Pimephales promelas) LC50: = 9640 mg/L, 96h flow-through (Pimephales promelas)	= 35390 mg/L EC50 Photobacterium phosphoreum 5 min	13299 mg/L EC50 = 48 h 9714 mg/L EC50 = 24 h

Persistence and Degradability Persistence is unlikely based on information available.

Bioaccumulation/ Accumulation No information available.

Mobility Will likely be mobile in the environment due to its volatility.

Component	log Pow
Isopropyl alcohol	0.05

13. Disposal considerations

Waste Disposal Methods Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

14. Transport information

DOT

UN-No UN1219
Proper Shipping Name Isopropanol
Hazard Class 3
Packing Group II

TDG

UN-No UN1219
Proper Shipping Name ISOPROPANOL
Hazard Class 3
Packing Group II

IATA

UN-No UN1219
Proper Shipping Name Isopropanol
Hazard Class 3
Packing Group II

IMDG/IMO

UN-No UN1219
Proper Shipping Name Isopropanol (Isopropyl alcohol)
Hazard Class 3
Packing Group II

15. Regulatory information

All of the components in the product are on the following Inventory lists: X = listed

International Inventories

Component	TSCA	DSL	NDSL	EINECS	ELINCS	NLP	PICCS	ENCS	AICS	IECSC	KECL
Isopropyl alcohol	X	X	-	200-661-7	-		X	X	X	X	X

Legend:
X - Listed
E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.
F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.
N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.
P - Indicates a commenced PMN substance
R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.
S - Indicates a substance that is identified in a proposed or final Significant New Use Rule
T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.
XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B).
Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.
Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

U.S. Federal Regulations

TSCA 12(b) Not applicable

SARA 313

Component	CAS-No	Weight %	SARA 313 - Threshold Values %
Isopropyl alcohol	67-63-0	>95	1.0

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	Yes
Fire Hazard	Yes
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

CWA (Clean Water Act) Not applicable

Clean Air Act Not applicable

OSHA Occupational Safety and Health Administration
Not applicable

CERCLA
Not applicable

California Proposition 65 This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Component	Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island
Isopropyl alcohol	X	X	X	-	X

U.S. Department of Transportation

Reportable Quantity (RQ):	N
DOT Marine Pollutant	N
DOT Severe Marine Pollutant	N

U.S. Department of Homeland Security
This product does not contain any DHS chemicals.

Other International Regulations

Mexico - Grade Serious risk, Grade 3

16. Other information

Prepared By
Regulatory Affairs
Thermo Fisher Scientific
Email: EMSDS.RA@thermofisher.com

Creation Date 01-Sep-2009
Revision Date 26-May-2017
Print Date 26-May-2017
Revision Summary This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS