

Date Prepared: 03/01/2011

Reviewed On: 02/11/2011

1 Identification of the substance/mixture and of the company/undertaking


- **Product Identifier**
- **Product Name:** HC Agar Base
- **Catalog Number:** 268510
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
BD Diagnostic Systems
7 Loveton Circle
Sparks, MD 21152
Telephone.: (410) 771 - 0100 or (800) 638 – 8663
- **Information Department:** Technical Service
- **Emergency telephone number:**
In case of a chemical emergency, spill, fire, exposure, or accident contact BD Diagnostic Systems (410) 771-0100 or (800)-638-8663, or ChemTrec at (800) 424-9300.

2 Composition/information on ingredients

- **Chemical characterization:** *Mixture*
- **Description:** *Mixture consisting of the following components.*

· Dangerous Components:		
7558-79-4	sodium phosphate, dibasic	6.41%
12125-02-9	ammonium chloride	2.57%
56-75-7	chloramphenicol	0.37%

3 Hazards identification

- **Classification of the substance or mixture**
- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**
 *Xn; Harmful*
R68/20/21: Harmful: possible risk of irreversible effects through inhalation and in contact with skin.
- **Classification system:**
The classification was made according to the latest editions of international substances lists, and expanded upon from company and literature data.
- **Label elements**
- **Labelling according to EU guidelines:**
The product has been classified and marked in accordance with regulations on hazardous materials.
- **Code letter and hazard designation of product:**
Xn Harmful
- **Hazard-determining components of labelling:**
chloramphenicol
- **Risk phrases:**
68/20/21 Harmful: possible risk of irreversible effects through inhalation and in contact with skin.
- **Safety phrases:**
 - 7 Keep container tightly closed.
 - 22 Do not breathe dust.
 - 24/25 Avoid contact with skin and eyes.
 - 36 Wear suitable protective clothing.

(Contd. on page 2)

Date Prepared: 03/01/2011

Reviewed On: 02/11/2011

Product Name: HC Agar Base

(Contd. of page 1)

· **NFPA ratings (scale 0-4)**



· **HMIS ratings (scale 0-4)**



4 First aid measures

· **General information**

Symptoms of poisoning may even occur after several hours; therefore provide medical observation for at least 48 hours after the accident.

· **After inhalation**

Supply fresh air. If required, provide artificial respiration. Keep patient warm. Seek medical advice.
In case of unconsciousness place patient on side position for transportation.

· **After skin contact** Immediately wash with water and soap and rinse thoroughly.

· **After eye contact** Rinse opened eye for 15 minutes under running water. Then consult a doctor.

· **After swallowing** Immediately call a doctor.

· **Information for doctor** Show this product label or this MSDS.

5 Firefighting measures

· **Suitable extinguishing agents**

CO₂, ABC multipurpose dry chemical or water spray. Fight larger fires with water spray or alcohol resistant foam.

· **Protective equipment:** No special measures required.

6 Accidental release measures

· **Personal precautions, protective equipment and emergency procedures** Not required.

· **Environmental precautions:** Wipe up with damp sponge or mop.

· **Methods and material for containment and cleaning up:** No special measures required.

· **Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage

· **Handling**

· **Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.

· **Information about protection against explosions and fires:** No special measures required.

· **Storage**

· **Requirements to be met by storerooms and receptacles:** < 30 °C

(Contd. on page 3)

Date Prepared: 03/01/2011

Reviewed On: 02/11/2011

Product Name: HC Agar Base

(Contd. of page 2)

- **Information about storage in one common storage facility:** Store away from oxidizing agents.
- **Further information about storage conditions:** Store in cool, dry conditions in well sealed containers.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see Section 7.

- **Components with limit values that require monitoring at the workplace:**

12125-02-9 ammonium chloride

REL	Short-term value: 20 mg/m ³ Long-term value: 10 mg/m ³
TLV	Short-term value: 20 mg/m ³ Long-term value: 10 mg/m ³

- **Additional information:** The lists that were valid during the creation were used as basis.
- **Personal Protective Equipment**
- **General protective and hygienic measures**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing.
Wash hands before breaks and at the end of work.
Store protective clothing separately.
Avoid contact with the eyes and skin.
- **Breathing equipment:**
In case of brief exposure, use a chemical fume hood or a NIOSH/MSHA-approved respirator.
- **Protection of hands:**



Chemical resistant gloves (i.e. nitrile, or equivalent).

- **Eye protection:** Safety glasses
- **Body protection:** Protective work clothing (lab coat).

9 Physical and chemical properties

- **General Information**

- **Appearance:**

Form:	Solid. Powder
Color:	Light beige
Odor:	Characteristic

- **pH-value:** 7.0 +/- 0.2

- **Change in condition**

Melting point/Melting range: Not determined
Boiling point/Boiling range: Not determined

- **Flash point:** Not applicable

- **Auto igniting:** Product is not self igniting.

- **Danger of explosion:** Product does not present an explosion hazard.

(Contd. on page 4)

Date Prepared: 03/01/2011

Reviewed On: 02/11/2011

Product Name: HC Agar Base

(Contd. of page 3)

· **Density:** Not determined

· **Solubility in / Miscibility with Water:** Soluble

· **Solvent content:**
Solids content: 100.0 %

10 Stability and reactivity

· **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.

· **Hazardous decomposition products:**

Carbon monoxide (CO) and carbon dioxide (CO₂)

Hydrogen chloride (HCl)

Phosphorus oxides (PO_x)

11 Toxicological information

· **Acute toxicity:**

· **LD/LC50 values that are relevant for classification:**

56-75-7 chloramphenicol

Oral LD50 2500 mg/kg (rat)

· **Primary irritant effect:**

· **on the skin:** No irritating effect.

· **on the eye:** No irritating effect.

· **Sensitization:** No sensitizing effects known.

· **Subacute to chronic toxicity:**

Target organs: blood, leukemia, aplastic anemia

Target organs: central nervous system, musculoskeletal system, and developmental abnormalities.

Target organs: blood, bone marrow, nerves and liver.

· **Additional toxicological information:**

The product shows the following dangers according to internally approved calculation methods for preparations:

California Proposition 65 - Warning: This product contains a chemical known to the State of California to cause cancer.

12 Ecological information

· **Acquatic toxicity:** No further relevant information available.

· **Ecotoxicological effects:**

· **Other information:**

The ecological effects have not been thoroughly investigated, but currently none have been identified.

· **Additional ecological information:**

· **General notes:** Water hazard class 1 (Self-assessment): slightly hazardous for water.

USA

(Contd. on page 5)

Date Prepared: 03/01/2011

Reviewed On: 02/11/2011

Product Name: HC Agar Base

(Contd. of page 4)

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation**
Smaller quantities can be disposed of with solid waste.
Dispose of material in accordance with federal (40 CFR 261.3), state and local requirements.
This product is not considered a RCRA hazardous waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to state and federal regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

14 Transport information

- **DOT regulations:**
- **Hazard class:** -
- **Land transport ADR/RID (cross-border)**
- **ADR/RID class:** -
- **Maritime transport IMDG:**
- **IMDG Class:** -
- **Marine pollutant:** No
- **Air transport ICAO-TI and IATA-DGR:**
- **ICAO/IATA Class:** -

15 Regulatory information

- **SARA Section 355 (extremely hazardous substances)**
None of the ingredients is listed.
- **SARA Section 313 (specific toxic chemical listings)**
None of the ingredients is listed.
- **TSCA (Toxic Substances Control Act)**

50-99-7	dextrose
9002-18-0	agar
8013-01-2	yeast extract
7558-79-4	sodium phosphate, dibasic
7778-77-0	potassium phosphate, monobasic
9000-71-9	casein
12125-02-9	ammonium chloride
144-55-8	sodium bicarbonate
56-75-7	chloramphenicol
7487-88-9	magnesium sulfate
7758-98-7	copper sulfate
- **California Proposition 65 - Chemicals known to cause cancer**

56-75-7	chloramphenicol
---------	-----------------

(Contd. on page 6)

**Material Safety Data Sheet**
acc. to ISO/DIS 11014

Date Prepared: 03/01/2011

Reviewed On: 02/11/2011

Product Name: HC Agar Base

(Contd. of page 5)

· California Proposition 65 - Chemicals known to cause reproductive toxicity for females:

None of the ingredients is listed.

· California Proposition 65 - Chemicals known to cause reproductive toxicity for males:

None of the ingredients is listed.

· California Proposition 65 - Chemicals known to cause developmental toxicity:

None of the ingredients is listed.

· Carcinogenic categories**· NTP (National Toxicology Program)**

56-75-7 chloramphenicol

R

· TLV (Threshold Limit Value established by ACGIH)

None of the ingredients is listed.

16 Other information

To the best of our knowledge, the information contained herein is accurate. However, neither Becton, Dickinson and Company or any of its subsidiaries assumes any liabilities whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we can not guarantee that these are the only hazards that exist.

· Department issuing MSDS:

Environmental, Health & Safety

Created by Michael J. Spinazzola

· Contact: Technical Service Representative

USA