


PCDH7 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP12322b	WB, IHC, E	H	O60245 , NP_002580.2 , NP_115832.1

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31610

Application Data: **Calculated MW: 116071 Da**



PCDH7 Antibody (C-term) (Cat. #AP12322b) western blot analysis in A549 cell line lysates (35ug/lane). This demonstrates the PCDH7 antibody detected the PCDH7 protein (arrow).



PCDH7 Antibody (C-term) (Cat. #AP12322b) immunohistochemistry analysis in formalin fixed and paraffin embedded human brain tissue followed by peroxidase conjugation of the secondary antibody and DAB staining. This data demonstrates the use of PCDH7 Antibody (C-term) for immunohistochemistry. Clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
5099	PCDH7

Other Names:

PCDH7; Protocadherin-7; BHPCDH

Target/Specificity:

This PCDH7 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 1038-1066 amino acids from the C-terminal region of human PCDH7.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

PCDH7 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

PCDH7 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
