

GPD2 Antibody (C-term)


Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP12502b	WB, IHC, E	H	P43304


Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31134

Application Data:

Calculated MW: 67kd Isoform 2. 80853 Da



GPD2 Antibody (C-term) (Cat. #AP12502b) western blot analysis in ZR-75-1 cell line lysates (35ug/lane). This demonstrates the GPD2 antibody detected the GPD2 protein (arrow).



GPD2 Antibody (C-term) (Cat. #AP12502b) immunohistochemistry analysis in formalin fixed and paraffin embedded human pancreas tissue followed by peroxidase conjugation of the secondary antibody and DAB staining. This data demonstrates the use of GPD2 Antibody (C-term) for immunohistochemistry. Clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
2820	GPD2

Other Names:

Glycerol-3-phosphate dehydrogenase, mitochondrial; GPD2;

Target/Specificity:

This GPD2 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 605-634 amino acids from the C-terminal region of human GPD2.

Application Notes:

The suggested dilution is:
ELISA 1:1,000

Western blotting 1:100~500
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

GPD2 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

GPD2 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
