


Mouse Hunk Antibody (Center)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14794c	WB, E	M	O88866 , NP_056570.1

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB30276

Application Data: Calculated MW: 79603 Da



Mouse Hunk Antibody (Center) (Cat. #AP14794c) western blot analysis in mouse lung tissue lysates (35ug/lane). This demonstrates the Hunk antibody detected the Hunk protein (arrow).

Gene ID:	Gene Symbol:
26559	Hunk

Other Names:

Hormonally up-regulated neu tumor-associated kinase;Hunk;Makv

Target/Specificity:

This Mouse Hunk antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 466-496 amino acids from the Central region of Mouse Hunk.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Mouse Hunk Antibody (Center) can be refrigerated at 2-8°C for up to 6 months. For long term

storage, place the at -20°C.

Precautions:

Mouse Hunk Antibody (Center) is for research use only and not for use in diagnostic or therapeutic procedures.
