


PRKRIR Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14857a	WB, E	H	O43422 , NP_004696.2
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34991

Application Data:

Calculated MW: 87704 Da



PRKRIR Antibody (N-term) (Cat. #AP14857a) western blot analysis in MCF-7 cell line lysates (35ug/lane). This demonstrates the PRKRIR antibody detected the PRKRIR protein (arrow).

Gene ID:	Gene Symbol:
5612	PRKRIR

Other Names:

52 kDa repressor of the inhibitor of the protein kinase;PRKRIR;DAP4; P52RIPK; THAP0

Target/Specificity:

This PRKRIR antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 101-130 amino acids from the N-terminal region of human PRKRIR.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

PRKRIR Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

PRKRIR Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
