


Mouse Cdk2 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP16161b	WB, E	M	P97377 , NP_904326.1 , NP_058036.1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB35468

Application Data:

Calculated MW: 38978 Da



Mouse Cdk2 Antibody (C-term) (Cat. #AP16161b) western blot analysis in mouse liver tissue lysates (35ug/lane). This demonstrates the Cdk2 antibody detected the Cdk2 protein (arrow).

Gene ID:	Gene Symbol:
12566	Cdk2

Other Names:

Cell division protein kinase 2;Cdk2;

Target/Specificity:

This Mouse Cdk2 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 226-254 amino acids from the C-terminal region of Mouse Cdk2.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Mouse Cdk2 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

Mouse Cdk2 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
