

# SAFETY DATA SHEET



R34488 Dichloromethane pesticide 1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

## SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Product name : Dichloromethane

Number : 000000020387

Product Use Description : Laboratory chemicals

Manufacturer or supplier's details : Honeywell International Inc.  
115 Tabor Road  
Morris Plains, NJ 07950-2546

For more information call : 1-800-368-0050  
+1-231-726-3171  
(Monday-Friday, 9:00am-5:00pm)

In case of emergency call : **Medical: 1-800-498-5701 or +1-303-389-1414**  
: **Transportation (CHEMTREC): 1-800-424-9300 or +1-703-527-3887**  
:  
: (24 hours/day, 7 days/week)

## SECTION 2. HAZARDS IDENTIFICATION

### Emergency Overview

Form : liquid

Color : colourless

Odor : sweet

### Classification of the substance or mixture

Classification of the substance or mixture : Skin irritation, Category 2  
Eye irritation, Category 2A  
Carcinogenicity, Category 2  
Specific target organ toxicity - single exposure, Category 3,  
Central nervous system

### GHS Label elements, including precautionary statements

# SAFETY DATA SHEET

**Honeywell**  
Riedel-de Haën™

R34488 Dichloromethane pesticide1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

Symbol(s)

:



Signal word

: Warning

Hazard statements

: Causes skin irritation.  
Causes serious eye irritation.  
May cause drowsiness and dizziness.  
Suspected of causing cancer.

Precautionary statements

: **Prevention:**  
Obtain special instructions before use.  
Do not handle until all safety precautions have been read and understood.  
Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.  
Wash skin thoroughly after handling.  
Use only outdoors or in a well-ventilated area.  
Wear protective gloves/protective clothing/eye protection/face protection.

**Response:**

IF ON SKIN: Wash with plenty of soap and water.  
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.  
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
IF exposed or concerned: Get medical advice/ attention.  
If skin irritation occurs: Get medical advice/ attention.  
If eye irritation persists: Get medical advice/ attention.  
Take off contaminated clothing and wash before reuse.

**Storage:**

Store in a well-ventilated place. Keep container tightly closed.  
Store locked up.

**Disposal:**

Dispose of contents/ container to an approved waste disposal plant.

**Carcinogenicity**

NTP:

Dichloromethane

75-09-2

Reasonably Anticipated to be a Human Carcinogen.

# SAFETY DATA SHEET



R34488 Dichloromethane pesticide 1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

IARC: Dichloromethane 75-09-2  
Group 2A: Probably carcinogenic to humans

ACGIH: Dichloromethane 75-09-2  
A3: Confirmed animal carcinogen

## SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Formula : CH<sub>2</sub>Cl<sub>2</sub>

Chemical nature : Substance

Chemical name	CAS-No.	Concentration
Dichloromethane	75-09-2	>=99.00 %

## SECTION 4. FIRST AID MEASURES

General advice : First aider needs to protect himself. Move out of dangerous area. If unconscious place in recovery position and seek medical advice. Take off all contaminated clothing immediately.

Inhalation : If breathed in, move person into fresh air. If symptoms persist, call a physician.

Skin contact : After contact with skin, wash immediately with plenty of water. Consult a physician.

Eye contact : Rinse thoroughly with plenty of water, also under the eyelids. Protect unharmed eye. Consult a physician.

Ingestion : When swallowed, allow water to be drunk. Call a physician immediately.

## SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media : Foam  
Carbon dioxide (CO<sub>2</sub>)  
Water spray  
Dry powder

# SAFETY DATA SHEET



R34488 Dichloromethane pesticide1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

- |   |  |
|---|--|
| Unsuitable extinguishing media                | : Do not use a solid water stream as it may scatter and spread fire.   |
| Specific hazards during firefighting          | : This product is not flammable at ambient temperatures and atmospheric pressure.<br>Exposure to decomposition products may be a hazard to health.<br>In case of fire hazardous decomposition products may be produced such as:<br>Phosgene<br>Chlorine (Cl <sub>2</sub> )<br>Carbon monoxide<br>Carbon dioxide (CO <sub>2</sub> )<br>Gaseous hydrogen chloride (HCl). |
| Special protective equipment for firefighters | : Wear self-contained breathing apparatus and protective suit.   |
| Further information                           | : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.<br>Cool containers/tanks with water spray.<br>Prevent fire extinguishing water from contaminating surface water or the ground water system.  |

## SECTION 6. ACCIDENTAL RELEASE MEASURES

- |                           |  |
|---------------------------|--|
| Personal precautions      | : Ensure adequate ventilation.<br>Evacuate personnel to safe areas.<br>Wear personal protective equipment. Unprotected persons must be kept away.<br>Do not breathe vapours or spray mist.   |
| Environmental precautions | : Prevent further leakage or spillage if safe to do so.<br>Do not let product enter drains.  |
| Methods for cleaning up   | : Ventilate the area.<br>Contain spillage, soak up with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and transfer to a container for disposal according to local / national regulations (see section 13). |

## SECTION 7. HANDLING AND STORAGE

### Handling

- |          |                                       |
|----------|---------------------------------------|
| Handling | : Wear personal protective equipment. |
|----------|---------------------------------------|

R34488 Dichloromethane pesticide 1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

Use only with adequate ventilation.  
Do not breathe vapours or spray mist.

Advice on protection against fire and explosion : Keep away from heat and sources of ignition.  
Normal measures for preventive fire protection.

**Storage**

Requirements for storage areas and containers : Store in original container.  
Keep containers tightly closed in a dry, cool and well-ventilated place.

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

Protective measures : Ensure that eyewash stations and safety showers are close to the workstation location.  
Legal requirements are to be considered in regard of the selection, use and care of personal protective equipment.  
Avoid exposure - obtain special instructions before use.

Engineering measures : Use with local exhaust ventilation.

Eye protection : Safety goggles

Hand protection : Impervious gloves  
Gloves must be inspected prior to use.  
Replace when worn.

Skin and body protection : Impervious clothing

Respiratory protection : In case of insufficient ventilation wear suitable respiratory equipment.

Hygiene measures : Keep working clothes separately.  
Take off all contaminated clothing immediately.  
Avoid contact with skin, eyes and clothing.  
Wash hands before breaks and at the end of workday.

**Exposure Guidelines**

Components	CAS-No.	Value	Control parameters	Update	Basis
Dichloromethane	75-09-2	TWA : Time weighted average	(50 ppm)	2008	ACGIH:US. ACGIH Threshold Limit Values

## SAFETY DATA SHEET

R34488 Dichloromethane pesticide1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

Dichloromethane	75-09-2	REF : Reference:	29 CFR 1910.1052	03 2012	OSHA:US. Specifically Regulated Substances (29 CFR 1910.1001- 1050)
Dichloromethane	75-09-2	TWA : Time weighted average	(25 ppm)	02 2006	OSHA:US. Specifically Regulated Substances (29 CFR 1910.1001- 1050)
Dichloromethane	75-09-2	OSHA_A CT : OSHA Action level:	(12.5 ppm)	02 2006	OSHA:US. Specifically Regulated Substances (29 CFR 1910.1001- 1050)
Dichloromethane	75-09-2	STEL : Short term exposure limit	(125 ppm)	02 2006	OSHA:US. Specifically Regulated Substances (29 CFR 1910.1001- 1050)

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

Physical state	: liquid
Color	: colourless
Odor	: sweet
Melting point/range	: -97 °C
Boiling point/boiling range	: 39 - 41 °C at 1,013 hPa
Flash point	: Note: Not applicable

# SAFETY DATA SHEET



R34488 Dichloromethane pesticide1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

Lower explosion limit	: 13 %(V)
Upper explosion limit	: 22 %(V)
Vapor pressure	: 453 hPa at 20 °C(68 °F)
Density	: 1.32 - 1.33 g/cm3 at 20 °C
Water solubility	: 20.0 g/l at 20 °C
Solubility in other solvents	: Note: soluble
Partition coefficient: n-octanol/water	: log Pow: 1.25
Ignition temperature	: 605 °C
Decomposition temperature	: > 120 °C Note: Decomposition temperature
Viscosity, dynamic	: 0.44 mPa.s at 20 °C
Molecular weight	: 84.93 g/mol

## SECTION 10. STABILITY AND REACTIVITY

Chemical stability	: Stable under recommended storage conditions.
Possibility of hazardous reactions	: Hazardous polymerisation does not occur. Vapours may form explosive mixture with air.
Conditions to avoid	: Heat, flames and sparks. Exposure to sunlight.

# SAFETY DATA SHEET



R34488 Dichloromethane pesticide1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

Incompatible materials to avoid	: Alkali metals Amines Bases Alkaline earth metals Powdered metals Strong oxidizing agents Strong acids
Hazardous decomposition products	: In case of fire hazardous decomposition products may be produced such as: Phosgene Chlorine (Cl <sub>2</sub> ) Carbon monoxide Carbon dioxide (CO <sub>2</sub> ) Gaseous hydrogen chloride (HCl).

## SECTION 11. TOXICOLOGICAL INFORMATION

Acute oral toxicity	: LD50: > 2,000 mg/kg Species: Rat Method: OECD Test Guideline 401 Note: No deaths
Acute inhalation toxicity	: LC50: 86 mg/l Species: Mouse
Acute dermal toxicity	: LD50: > 2,000 mg/kg Species: Rat Method: OECD Test Guideline 402
Skin irritation	: Species: Rabbit Result: Irritating to skin. Method: OECD Test Guideline 404
Eye irritation	: Species: rabbit eye Result: Irritating to eyes.
Sensitisation	: Species: Mouse Result: non-sensitizing Method: OECD 429



R34488 Dichloromethane pesticide 1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

Dichloromethane : Test Method: Ames test  
Result: positive

: Test Method: In vitro gene mutation study in mammalian cells  
Cell type: Chinese Hamster Ovary Cells  
Result: positive

: Test Method: Unscheduled DNA synthesis  
Result: positive  
Note: Liver cells Mouse

Further information : Note: Confirmed animal carcinogen with unknown relevance to humans.

**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity effects**

Toxicity to fish : LC50: 193 mg/l  
Exposure time: 96 h  
Species: Pimephales promelas (fathead minnow)

: LC50: 97 mg/l  
Exposure time: 48 h  
Species: Fish

: NOEC: 142 mg/l  
Exposure time: 28 d  
Species: Pimephales promelas (fathead minnow)  
Note: mortality

Toxicity to daphnia and other aquatic invertebrates : LC50: 220 mg/l  
Exposure time: 48 h  
Species: Daphnia (water flea)

: LC50: 27 mg/l  
Exposure time: 48 h  
Species: Daphnia magna (Water flea)

Toxicity to algae : Note: no data available

## SAFETY DATA SHEET

R34488 Dichloromethane pesticide 1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

Toxicity to bacteria : LC0: 500 mg/l  
Species: Pseudomonas putida

: EC50: 2,590 mg/l  
Exposure time: 40 min  
Species: activated sludge  
Method: OECD 209

**Elimination information (persistence and degradability)**

Bioaccumulation : Note: No bioaccumulation is to be expected (log Pow <= 4).

Biodegradability : Result: Readily biodegradable  
Value: 68 %  
Method: OECD 301 D

**Further information on ecology****SECTION 13. DISPOSAL CONSIDERATIONS**

Disposal methods : Observe all Federal, State, and Local Environmental regulations.

**SECTION 14. TRANSPORT INFORMATION**

**DOT** UN/ID No. : UN 1593  
Proper shipping name : DICHLOROMETHANE  
Class : 6.1  
Packing group : III  
Hazard Labels : 6.1

**IATA** UN/ID No. : UN 1593  
Description of the goods : DICHLOROMETHANE  
Class : 6.1  
Packaging group : III  
Hazard Labels : 6.1  
Packing instruction (cargo aircraft) : 663  
Packing instruction (passenger aircraft) : 655  
Packing instruction (passenger aircraft) : Y642

# SAFETY DATA SHEET



R34488 Dichloromethane pesticide 1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

<b>IMDG</b>	UN/ID No.	: UN 1593
	Description of the goods	: DICHLOROMETHANE
	Class	: 6.1
	Packaging group	: III
	Hazard Labels	: 6.1
	EmS Number	: F-A, S-A
	Marine pollutant	: no

## SECTION 15. REGULATORY INFORMATION

### Inventories

US. Toxic Substances Control Act : On TSCA Inventory

Australia. Industrial Chemical (Notification and Assessment) Act : On the inventory, or in compliance with the inventory

Canada. Canadian Environmental Protection Act (CEPA). Domestic Substances List (DSL) : All components of this product are on the Canadian DSL

Japan. Kashin-Hou Law List : On the inventory, or in compliance with the inventory

Korea. Toxic Chemical Control Law (TCCL) List : On the inventory, or in compliance with the inventory

Philippines. The Toxic Substances and Hazardous and Nuclear Waste Control Act : On the inventory, or in compliance with the inventory

China. Inventory of Existing Chemical Substances : On the inventory, or in compliance with the inventory

New Zealand. Inventory of Chemicals (NZIoC), as published by ERMA New Zealand : On the inventory, or in compliance with the inventory

### National regulatory information

US. EPA CERCLA Hazardous Substances (40 CFR 302) : The following component(s) of this product is/are subject to release reporting under 40 CFR 302 when release exceeds the Reportable Quantity (RQ):

## SAFETY DATA SHEET



R34488 Dichloromethane pesticide1,00LFL

000000020387

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

	Reportable quantity: 1000 lbs	
	: Dichloromethane	75-09-2
<b>SARA 302 Components</b>	: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.	
<b>SARA 313 Components</b>	: The following components are subject to reporting levels established by SARA Title III, Section 313:	
	: Dichloromethane	75-09-2
<b>SARA 311/312 Hazards</b>	: Acute Health Hazard Chronic Health Hazard	
<b>CERCLA Reportable Quantity</b>	: 1001 lbs	
<b>California Prop. 65</b>	: WARNING! This product contains a chemical known to the State of California to cause cancer. Dichloromethane	
		75-09-2
<b>Massachusetts RTK</b>	: Dichloromethane	75-09-2
<b>New Jersey RTK</b>	: Dichloromethane	75-09-2
<b>Pennsylvania RTK</b>	: Dichloromethane	75-09-2

## SECTION 16. OTHER INFORMATION

	<b>HMIS III</b>	<b>NFPA</b>
Health hazard	: 2*	2
Flammability	: 1	1
Physical Hazard	: 0	
Instability	:	0

\* - Chronic health hazard

Hazard rating and rating systems (e.g. HMIS® III, NFPA): This information is intended solely for the use of individuals trained in the particular system.

## Further information

# SAFETY DATA SHEET



R34488 Dichloromethane pesticide1,00LFL

**000000020387**

Version 1.0

Revision Date 10/02/2016

Print Date 12/20/2016

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text. Final determination of suitability of any material is the sole responsibility of the user. This information should not constitute a guarantee for any specific product properties.

Changes since the last version are highlighted in the margin. This version replaces all previous versions.

Prepared by Honeywell Performance Materials and Technologies Product Stewardship Group