


HCN1 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14228b	WB, E	H	NP_066550.2 , O60741
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34236

Application Data: Calculated MW: 98796 Da



HCN1 Antibody (C-term) (Cat. #AP14228b) western blot analysis in HeLa cell line lysates (35ug/lane). This demonstrates the HCN1 antibody detected the HCN1 protein (arrow).

Gene ID:	Gene Symbol:
348980	HCN1

Other Names:

Potassium/sodium hyperpolarization-activated cyclic nucleotide-gated channel 1; HCN1; BCNG1

Target/Specificity:

This HCN1 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 859-889 amino acids from the C-terminal region of human HCN1.

Application Notes:

The suggested dilution is:
 ELISA 1:1,000
 Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

HCN1 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

HCN1 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
