SECTION 1: Identification

1.1. Product Identifier

Trade Name or Designation: VeriSpec™ Beryllium Standard for ICP 1000 ppm in 2% HNO₃/HF

Manufactured and Tested in an ISO 17025/Guide 34 Accredited Facility

Product Number: RV010334

Other Identifying Product Numbers: RV010334-100N, RV010334-250N, RV010334-30N, RV010334-500N, RV010334-50N

1.2. Recommended Use and Restrictions on Use

Calibration Standard

1.3. Details of the Supplier of the Safety Data Sheet

Company: Ricca Chemical Company

Address: 448 West Fork Drive

Arlington, TX 76012 USA

Telephone: 888-467-4222

1.4. Emergency Telephone Number (24 hr)

CHEMTREC (USA) 800-424-9300 CHEMTREC (International) 1+ 703-527-3887

SECTION 2: Hazard(s) Identification

2.1. Classification of the Substance or Mixture (in accordance with OSHA HCS 29 CFR 1910.1200)

For the full text of the Hazard and Precautionary Statements listed below, see Section 16.

		Hazard	
Hazard Class	Category	Statement	Precautionary Statements
Skin Corrosion / Irritation	Category 2	H315	P264, P280, P302+P352, P321, P332+P313, P362
Eye Damage / Irritation	Category 2A	H319	P264, P280, P305+P351+P338, P337+P313
Skin Sensitizer	Category 1	H317	P261, P272, P280, P302+P352, P332+P313,
			P321, P363, P501
Carcinogenicity	Category 1B	H350	P201, P202, P280, P308+P313, P405, P501
Specific Target Organs/Systemic Toxicity Following Repeated	Category 1	H372	P260, P264, P270, P314, P501
Exposure			

Product Number: RV010334 Page 1 of 12



2.2. GHS Label Elements Pictograms:





Signal Word: Danger

Hazard Statements:

Hazard Number	Hazard Statement
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H350	May cause cancer.
H372	Causes damage to organs through prolonged or repeated exposure.

Precautionary Statements:

Precautionary Number	Precautionary Statement
P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P260	Do not breathe dust, fumes or mist.
P261	Avoid breathing dust, fumes or mist.
P264	Wash arms, hands and face thoroughly after handling.
P270	Do not eat, drink or smoke when using this product.
P272	Contaminated work clothing must not be allowed out of the workplace.
P280	Wear protective gloves and eye protection.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to d
	Continue rinsing.
P308+P313	IF exposed or concerned: Get medical attention.
P314	Get medical attention if you feel unwell.
P321	Specific treatment (Wash areas of contact with water immediately).
P332+P313	If skin irritation occurs: Get medical attention.
P337+P313	If eye irritation persists: Get medical attention.
P362	Take off contaminated clothing and wash it before reuse.
P363	Wash contaminated clothing before reuse.
P405	Store locked up.
P501	Dispose of contents in accordance with local, state, federal and international regulations.

Product Number: RV010334 Page 2 of 12

2.3. WHMIS Classification

WHMIS classification is not included based on the recommended option (Option 4) found in the Canada Gazette Part II, Vol. 149, No.3, page 458

2.4. Hazards not Otherwise Classified or Covered by GHS

Data not available.

SECTION 3: Composition / Information on Ingredients

3.1. Components of Substance or Mixture

Chemical Name	Formula	Molecular Weight	CAS Number	Weight%
Water	H_2O	18.01 g/mol	7732-18-5	96.02%
Nitric Acid	HNO₃	63.01 g/mol	7697-37-2	2.00%
Beryllium nitrate	BeN₂O ₆	133.02 g/mol	13597-99-4	1.48%
Hydrofluoric Acid	HF	20.00 g/mol	7664-39-3	0.50%

SECTION 4: First-Aid Measures

4.1. General First Aid Information

Eye Contact: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

Inhalation: Not expected to require first aid. If necessary, remove to fresh air.

Skin Contact: IF ON SKIN: Wash with plenty of soap and water.

Ingestion: No action required to be taken. If necessary, dilute with water.

4.2. Most Important Symptoms and Effects, Acute and Delayed

May cause mild irritation to areas of contact.

4.3. Medical Attention or Special Treatment Needed

Specific treatment (Wash areas of contact with water immediately).

SECTION 5: Fire-Fighting Measures

5.1. Extinguishing Media

Not considered to be a fire or explosion hazard.

5.2. Specific Hazards Arising from the Substance or Mixture

Not considered to be a fire or explosion hazard.

5.3. Special Protective Equipment for Firefighters

Wear protective clothing and NIOSH-approved breathing equipment appropriate for the surrounding fire.

Product Number: RV010334 Page 3 of 12

SECTION 6: Accidental Release Measures

6.1. Personal Precautions, Protective Equipment and Emergency ProceduresWear protective gloves and eye protection.

6.2. Cleanup and Containment Methods and Materials

Absorb with suitable material and dispose of in accordance with local regulations.

SECTION 7: Handling and Storage

7.1. Precautions for Safe Handling and Storage ConditionsStore locked up.

SECTION 8: Exposure Controls / Personal Protection

8.1. Control Parameters

Chemical Name	Limit Type	Country	Exposure Limit	Information Source
Beryllium nitrate (13597-99-4)	TWA	USA	2 μg/m³ TWA (as Be)	U.S OSHA - Final PELs - Time Weighted
				Averages (TWAs)
Beryllium nitrate (13597-99-4)	TLV-TWA	USA	0.00005 mg/m³ TWA (inhalable fraction ACGIH - Threshold Limit Values - Time	
			as Be)	Weighted Averages (TLV-TWA)
Beryllium nitrate (13597-99-4)	PEL-Ceiling	USA	5 μg/m³ Ceiling (as Be)	U.S OSHA - Final PELs - Ceiling Limits
Hydrofluoric Acid (7664-39-3)	TWA	USA	3 ppm TWA (as F)	U.S OSHA - Final PELs - Time Weighted
				Averages (TWAs)
Hydrofluoric Acid (7664-39-3)	TWA	USA	2.5 mg/m³ TWA (as F)	U.S OSHA - Final PELs - Time Weighted
			2.5 mg/m³ TWA (dust)	Averages (TWAs)
Hydrofluoric Acid (7664-39-3)	TLV-Ceiling	USA	2 ppm Ceiling (as F)	ACGIH - Threshold Limit Values - Ceilings
				(TLV-C)
Hydrofluoric Acid (7664-39-3)	TLV-TWA	USA	2.5 mg/m ³ TWA (as F)	ACGIH - Threshold Limit Values - Time
				Weighted Averages (TLV-TWA)
Hydrofluoric Acid (7664-39-3)	TLV-TWA	USA	0.5 ppm TWA (as F)	ACGIH - Threshold Limit Values - Time
				Weighted Averages (TLV-TWA)
Nitric Acid (7697-37-2)	TWA	USA	2 ppm TWA	U.S OSHA - Final PELs - Time Weighted
			5 mg/m³ TWA	Averages (TWAs)
Nitric Acid (7697-37-2)	TLV-STEL	USA	4 ppm STEL	ACGIH - Threshold Limit Values - Short
				Term Exposure Limits (TLV-STEL)
Nitric Acid (7697-37-2)	TLV-TWA	USA	2 ppm TWA	ACGIH - Threshold Limit Values - Time
				Weighted Averages (TLV-TWA)

8.2. Exposure Controls

Engineering Controls: No specific controls are needed. Normal room ventilation is adequate. **Respiratory Protection:** No specific controls are needed. Normal room ventilation is adequate

Product Number: RV010334 Page 4 of 12

Skin Protection: Wear protective gloves and eye protection. **Eye Protection:** Wear protective gloves and eye protection.

8.3. Personal Protective Equipment

Wear protective gloves and eye protection.

SECTION 9: Physical and Chemical Properties

9.1. Basic Physical and Chemical Properties

Appearance: Data not available.

Physical State: Liquid

Odor: Data not available.

Odor Threshold: Data not available.

pH: Data not available.

Melting/Freezing Point: Data not available.

Initial Boiling Point /Range: Data not available.

Flash Point: Data not available.

Evaporation Rate: Data not available.

Flammability: Data not available.

Flammability/Explosive Limits: Data not available.

Vapor Pressure: Data not available.

Vapor Density: Data not available.

Relative Density: 1.00

Solubility: Data not available.

Partition Coefficient (n-Octanol/Water): Data not available.

Auto-Ignition Temperature: Data not available.

Decomposition Temperature: Data not available.

Viscosity: Data not available.

ExplosiveProperties: Data not available.

Oxidizing Properties: Data not available.

SECTION 10: Stability and Reactivity

10.1. Reactivity and Chemical Stability

Stable under normal conditions of use and storage.

10.2. Possibility of Hazardous Reactions

Data not available.

Product Number: RV010334 Page 5 of 12

10.3. Conditions to Avoid and Incompatible Materials

Protect from freezing and physical damage.

10.4. Hazardous Decomposition Products

May emit irritating fumes when heated to decomposition.

SECTION 11: Toxicological Information

11.1. Information on Toxicological Effects

Acute Toxicity - Oral Exposure:

Not applicable.

Acute Toxicity - Dermal Exposure:

Not applicable.

Acute Toxicity - Inhalation Exposure:

Not applicable.

Acute Toxicity - Other Information:

Data not available.

Skin Corrosion and Irritation:

Causes skin irritation. Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection. IF ON SKIN: Wash with plenty of soap and water. Specific treatment (Wash areas of contact with water immediately). If skin irritation occurs: Get medical attention. Take off contaminated clothing and wash it before reuse.

Serious Eye Damage and Irritation:

Causes serious eye irritation. Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.

Respiratory Sensitization:

Not applicable.

Skin Sensitization:

May cause an allergic skin reaction. Avoid breathing dust, fumes or mist. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves and eye protection. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical attention. Specific treatment (Wash areas of contact with water immediately). Wash contaminated clothing before reuse. Dispose of contents in accordance with local, state, federal and international regulations.

Germ Cell Mutagenicity:

Not applicable.

Carcinogenicity:

May cause cancer. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves and eye protection. IF exposed or concerned: Get medical attention. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Product Number: RV010334 Page 6 of 12

Reproductive Toxicity:

Not applicable.

Specific Target Organ Toxicity from Single Exposure:

Not applicable.

Specific Target Organ Toxicity from Repeated Exposure:

Causes damage to organs through prolonged or repeated exposure. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. Get medical attention if you feel unwell. Dispose of contents in accordance with local, state, federal and international regulations.

Aspiration Hazard:

Not applicable.

Additional Toxicology Information:

Data not available.

SECTION 12: Ecological Information

12.1. Ecotoxicity

Not applicable.

12.2. Persistence and Degradability

Data not available.

12.3. Bioaccumulative Potential

Data not available.

12.4. Mobility in Soil

Data not available.

12.5. Other Adverse Ecological Effects

Data not available.

SECTION 13: Disposal Considerations

13.1. Waste Treatment Methods

Data not available.

Product Number: RV010334 Page **7** of **12**



SECTION 14: Transportation Information



Not regulated according to DOT Regulations.

Not regulated according to IATA Regulations.

SECTION 15: Regulatory Information

15.1. Occupational Safety and Health Administration (OSHA) Hazards

Not listed.

15.2. Superfund Amendments and Reauthorization Act (SARA) 302 Extremely Hazardous Substances

Hydrofluoric Acid (CAS # 7664-39-3): 100 lb EPCRA RQ Hydrofluoric Acid (CAS # 7664-39-3): 100 lb TPQ Nitric Acid (CAS # 7697-37-2): 1000 lb EPCRA RQ Nitric Acid (CAS # 7697-37-2): 1000 lb TPQ

15.3. Superfund Amendments and Reauthorization Act (SARA) 311/312 Hazardous Chemicals

Beryllium nitrate (CAS # 13597-99-4): 1 lb final RQ (listed under Beryllium nitrate); 0.454 kg final RQ (listed under Beryllium nitrate)

Beryllium nitrate (CAS # 13597-99-4): 1 lb final RQ; 0.454 kg final RQ Hydrofluoric Acid (CAS # 7664-39-3): 100 lb final RQ; 45.4 kg final RQ Nitric Acid (CAS # 7697-37-2): 1000 lb final RQ; 454 kg final RQ

Product Number: RV010334 Page 8 of 12

15.4. Superfund Amendments and Reauthorization Act (SARA) 313 Toxic Release Inventory (TRI)

Beryllium nitrate (CAS # 13597-99-4): 0.1 % de minimis concentration (listed under Chemical Category N050)

Hydrofluoric Acid (CAS # 7664-39-3): 1.0 % de minimis concentration

Nitric Acid (CAS # 7697-37-2): 1.0 % de minimis concentration

15.5. Massachusetts Right-to-Know Substance List

Beryllium nitrate (CAS # 13597-99-4): Present

Hydrofluoric Acid (CAS # 7664-39-3): Extraordinarily hazardous

Nitric Acid (CAS # 7697-37-2): Extraordinarily hazardous

15.6. Pennsylvania Right-to-Know Hazardous Substances

Beryllium nitrate (CAS # 13597-99-4): Environmental hazard

Beryllium nitrate (CAS # 13597-99-4): Present

Hydrofluoric Acid (CAS # 7664-39-3): Environmental hazard

Hydrofluoric Acid (CAS # 7664-39-3): Present

Nitric Acid (CAS # 7697-37-2): Environmental hazard

Nitric Acid (CAS # 7697-37-2): Present

Water (CAS # 7732-18-5): Present

15.7. New Jersey Worker and Community Right-to-Know Components

Beryllium nitrate (CAS # 13597-99-4): carcinogen

Beryllium nitrate (CAS # 13597-99-4): sn 0225

Beryllium nitrate (CAS # 13597-99-4): sn 2163

Beryllium nitrate (CAS # 13597-99-4): SN 2163 500 lb TPQ (Category Code N050)

Beryllium nitrate (CAS # 13597-99-4): sn 3722

Beryllium nitrate (CAS # 13597-99-4): SN 3722 500 lb TPQ (water dissociable, Category Code N511)

Beryllium nitrate (CAS # 13597-99-4): sn 4097

Beryllium nitrate (CAS # 13597-99-4): sn 4101

Hydrofluoric Acid (CAS # 7664-39-3): corrosive

Hydrofluoric Acid (CAS # 7664-39-3): sn 0936

Hydrofluoric Acid (CAS # 7664-39-3): sn 3759

Hydrofluoric Acid (CAS # 7664-39-3): SN 3759 100 lb TPQ; SN 1014 500 lb TPQ (Hydrogen fluoride gas only)

Nitric Acid (CAS # 7697-37-2): corrosive; reactive - second degree

Nitric Acid (CAS # 7697-37-2): sn 1356

Nitric Acid (CAS # 7697-37-2): SN 1356 500 lb TPQ

Nitric Acid (CAS # 7697-37-2): sn 3722

Nitric Acid (CAS # 7697-37-2): SN 3722 500 lb TPQ (water dissociable, Category Code N511)

15.8. California Proposition 65

Beryllium nitrate (CAS # 13597-99-4): carcinogen, 10/1/1987

Product Number: RV010334 Page 9 of 12

15.9. Canada Domestic Substances List / Non-Domestic Substances List (DSL/NDSL)

Beryllium nitrate (CAS # 13597-99-4): Present (NDSL) Hydrofluoric Acid (CAS # 7664-39-3): Present (DSL) Nitric Acid (CAS # 7697-37-2): Present (DSL) Water (CAS # 7732-18-5): Present (DSL)

15.10. United States of America Toxic Substances Control Act (TSCA) List

Beryllium nitrate (CAS # 13597-99-4): Present Hydrofluoric Acid (CAS # 7664-39-3): Present [T] Nitric Acid (CAS # 7697-37-2): Present Water (CAS # 7732-18-5): Present

15.11. European Inventory of Existing Commercial Chemical Substances (EINECS), European List of Notified Chemical Substances (ELINCS), and No Longer Polymers (NLP)

Not listed.

SECTION 16: Other Information

16.1. Full Text of Hazard Statements and Precautionary Statements

Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause cancer. Causes damage to organs through prolonged or repeated exposure.

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves and eye protection.

IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed or concerned: Get medical attention. Get medical attention if you feel unwell. Specific treatment (Wash areas of contact with water immediately). If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing and wash it before reuse.

Store locked up.

Dispose of contents in accordance with local, state, federal and international regulations.

16.2. Miscellaneous Hazard Classes

Canadian Carcinogenicity Hazard Class: Not Applicable.

Physical Hazards Not Otherwise Classified (PHNOC): Not Applicable.

Health Hazards Not Otherwise Classified (HHNOC): Not Applicable.

Biohazardous Infectious Materials Hazard Class: Not Applicable.

Product Number: RV010334 Page 10 of 12


16.3. National Fire Protection Association (NFPA) Rating

Health: 1

Flammability: 0

Reactivity: 0

Special Hazard:



Product Number: RV010334 Page 11 of 12

16.4. Document Revision

Last Revision Date: 9/7/2016

DISCLAIMER

When handled properly by qualified personnel, the product described herein does not present a significant health or safety hazard. Alteration of its characteristics by concentration, evaporation, addition of other substances, or other means may present hazards not specifically addressed herein and which must be evaluated by the user. The information furnished herein is believed to be accurate and represents the best data currently available to us. No warranty, expressed or implied, is made and RICCA CHEMICAL COMPANY assumes no legal responsibility or liability whatsoever resulting from its use.

Product Number: RV010334 Page 12 of 12