


ACSL4 Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14406a	WB, E	H	NP_075266.1 , O60488 , NP_004449.1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34356

Application Data:

Calculated MW: 79188 Da



ACSL4 Antibody (N-term) (Cat. #AP14406a) western blot analysis in 293 cell line lysates (35ug/lane). This demonstrates the ACSL4 antibody detected the ACSL4 protein (arrow).

Gene ID:	Gene Symbol:
2182	ACSL4

Other Names:

Long-chain-fatty-acid--CoA ligase 4; ACSL4; ACS4; FAACL4; LACS4

Target/Specificity:

This ACSL4 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 27-56 amino acids from the N-terminal region of human ACSL4.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

ACSL4 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

ACSL4 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
