



Material Safety Data Sheet

Catalog Number: 100955
Revision date: 26-Apr-2006

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY INFORMATION

Catalog Number: 100955

Product name: PHENAZINE METHOSULFATE

Synonyms: N-Methylphenazonium Methosulfate

Supplier:

MP Biomedicals, LLC
29525 Fountain Parkway
Solon, OH 44139
tel: 440-337-1200

Emergency telephone number: CHEMTREC: 1-800-424-9300 (1-703-527-3887)

2. COMPOSITION/INFORMATION ON INGREDIENTS

Components	CAS Number	Weight %	ACGIH Exposure Limits:	OSHA Exposure Limits:
PHENAZINE METHOSULFATE	299-11-6	90 - 100%	None	None

3. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW: May cause skin irritation and/or dermatitis

Principle routes of exposure: Skin

Inhalation: May cause irritation of respiratory tract

Ingestion: May be harmful if swallowed.

Skin contact: May cause allergic skin reaction

Eye contact: Avoid contact with eyes

Statements of hazard MAY CAUSE ALLERGIC SKIN REACTION.

Statement of Spill or Leak - ANSI Label Eliminate all ignition sources. Absorb and/or contain spill with inert materials (e.g., sand, vermiculite). Then place in appropriate container. For large spills, use water spray to disperse vapors, flush spill area. Prevent runoff from entering waterways or sewers.

4. FIRST AID MEASURES

General advice: In the case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

Inhalation: Move to fresh air. Call a physician immediately.

Skin contact: Rinse immediately with plenty of water and seek medical advice

Ingestion: Do not induce vomiting without medical advice.

Eye contact: In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

Protection of first-aiders: No information available

Medical conditions aggravated by exposure: None known

5. FIRE FIGHTING MEASURES

Suitable extinguishing media:	Use dry chemical, CO ₂ , water spray or "alcohol" foam
Specific hazards:	Burning produces irritant fumes.
Unusual hazards:	None known
Special protective equipment for firefighters:	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear
Specific methods:	Water mist may be used to cool closed containers.
Flash point:	Not determined
Autoignition temperature:	Not determined
NFPA rating:	
NFPA Health:	1
NFPA Flammability:	1
NFPA Reactivity:	0

6. ACCIDENTAL RELEASE MEASURES

Personal precautions:	Use personal protective equipment.
Environmental precautions:	Prevent product from entering drains.
Methods for cleaning up:	Sweep up and shovel into suitable containers for disposal.

7. HANDLING AND STORAGE

Storage:
+4°C
PROTECT FROM LIGHT

Handling:	Use only in area provided with appropriate exhaust ventilation.
Safe handling advice:	Wear personal protective equipment.
Incompatible products:	Oxidising and spontaneously flammable products

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering measures: Ensure adequate ventilation.

PERSONAL PROTECTIVE EQUIPMENT

Respiratory protection: Breathing apparatus only if aerosol or dust is formed.

Hand protection: Pvc or other plastic material gloves

Skin and body protection: Usual safety precautions while handling the product will provide adequate protection against this potential effect.

Eye protection: Safety glasses with side-shields

Hygiene measures: Handle in accordance with good industrial hygiene and safety practice.



9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Powder
Formula:	C ₁₃ H ₁₁ N ₂ • CH ₃ SO ₄
Molecular weight:	306.3
Melting point/range:	155-157°C (dec.)
Boiling point/range:	No Data available at this time.
Density:	No data available
Vapor pressure:	No data available

Evaporation rate:	No data available
Vapor density:	No data available
Solubility (in water):	Soluble
Flash point:	Not determined
Autoignition temperature:	Not determined

10. STABILITY AND REACTIVITY

Stability:	Stable under recommended storage conditions.
Polymerization:	None under normal processing.
Hazardous decomposition products:	Nitrogen oxides (NOx)/ammonia/CN- , Sulphur oxides
Materials to avoid:	Strong oxidising agents
Conditions to avoid:	Exposure to air or moisture over prolonged periods.

11. TOXICOLOGICAL INFORMATION

Product Information

Acute toxicity

Components

PHENAZINE METHOSULFATE

RTECS Number:

SG1645000

Selected LD50s and LC50s

Not Determined

Chronic toxicity:	Chronic exposure may cause nausea and vomiting, higher exposure causes unconsciousness.
Local effects:	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting.
Specific effects:	May include moderate to severe erythema (redness) and moderate edema (raised skin), nausea, vomiting, headache.
Primary irritation:	No data is available on the product itself.
Carcinogenic effects:	No data is available on the product itself.
Mutagenic effects:	No data is available on the product itself.
Reproductive toxicity:	No data is available on the product itself.

12. ECOLOGICAL INFORMATION

Mobility:	No data available
Bioaccumulation:	No data available
Ecotoxicity effects:	No data available
Aquatic toxicity:	May cause long-term adverse effects in the aquatic environment.

Components	U.S. DOT - Appendix B - Marine Pollutan	U.S. DOT - Appendix B - Severe Marine Pollutants	United Kingdom - The Red List:
PHENAZINE METHOSULFATE	Not Listed	Not Listed	Not Listed
Components	Germany VCI (WGK)	World Health Organization (WHO) - Drinking Water	Ecotoxicity - Fish Species Data
PHENAZINE METHOSULFATE	Not Listed	Not Listed	Not Listed
Components	Ecotoxicity - Freshwater Algae Data	Ecotoxicity - Microtox Data	Ecotoxicity - Water Flea Data
PHENAZINE METHOSULFATE	Not Listed	Not Listed	Not Listed
Components	EPA - ATSDR Priority List	EPA - HPV Challenge Program Chemical List	California - Priority Toxic Pollutants
PHENAZINE METHOSULFATE	Not Listed	Not Listed	Not Listed

Components
PHENAZINE METHOSULFATE

California - Priority Toxic Pollutants
Not Listed

California - Priority Toxic Pollutants
Not Listed

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products:

Waste disposal must be in accordance with appropriate Federal, State, and local regulations. This product, if unaltered by use, may be disposed of by treatment at a permitted facility or as advised by your local hazardous waste regulatory authority. Residue from fires extinguished with this material may be hazardous.

Contaminated packaging:

Do not re-use empty containers

14. TRANSPORT INFORMATION

UN/Id No:

Not regulated

DOT:

Proper shipping name:

Not Regulated

Components
PHENAZINE METHOSULFATE

U.S. DOT - Appendix A Table 1 - Reportable Quantities
Not Listed

TDG (Canada):

WHMIS hazard class:

Non-controlled

IMDG/IMO

IMDG - Hazard Classifications

Not Applicable

Components
PHENAZINE METHOSULFATE

U.S. DOT - Appendix B - Marine Pollutan
Not Listed

U.S. DOT - Appendix B - Severe Marine
Pollutants
Not Listed

IMO-labels:

15. REGULATORY INFORMATION

International Inventories

Components

PHENAZINE METHOSULFATE

Inventory - United States TSCA - Sect. 8(b)

Present

Canada DSL Inventory List -

Present

Inventory - China:

Present

EU EINECS List -

206-072-1; C13H11N2.CH3O4S

U.S. regulations:

ComponentsPHENAZINE
METHOSULFATE

California Proposition 65 -	Massachusetts Right to Know List:	New Jersey Right to Know List:	Pennsylvania Right to Know List:
Not Listed	Not Listed	Not Listed	Not Listed

ComponentsPHENAZINE
METHOSULFATE

Florida substance List:	Rhode Island Right to Know List:	Illinois - Toxic Air Contaminants	Connecticut - Hazardous Air Pollutants
Not Listed	Not Listed	Not Listed	Not Listed

ComponentsPHENAZINE
METHOSULFATE

SARA 313 Emission reporting/Toxic Release of Chemicals	CERCLA/SARA - Section 302 Extremely Haz	NTP:	IARC:
Not Listed	Not Listed	None	None

SARA 313 Notification:

The above is your notification as to the SARA 313 listing for this product(s) pursuant to Section 313 of Title III of the Superfund Ammendments and Reauthorization Act of 1986 and 40 CFR Part 372.

If you are unsure if you are subject to the reporting requirements of Section 313, or need more information, please call the EPA Emergency Planning and Community Right-To-Know Information Hotline: (800) 535-0202 or (202) 479-2499 (in Washington, DC or Alaska).

State Notification:

The above information is your notice as to the Right-to-Know listings of the stated product(s). Individual states will list chemicals for a variety of reasons including, but not limited to, the compounds toxicity; carcinogenic, tumorigenic and/or reproductive hazards; and the compounds environmental impact if accidentally released.

16. OTHER INFORMATION

Prepared by: Health & Safety

Disclaimer: The information and recommendations contained herein are based upon tests believed to be reliable. However, MP Biomedicals does not guarantee the accuracy or completeness NOR SHALL ANY OF THIS INFORMATION CONSTITUTE A WARRANTY, WHETHER EXPRESSED OR IMPLIED, AS TO THE SAFETY OF THE GOODS, THE MERCHANTABILITY OF THE GOODS, OR THE FITNESS OF THE GOODS FOR A PARTICULAR PURPOSE. Adjustment to conform to actual conditions of usage maybe required. MP Biomedicals assumes no responsibility for results obtained or for incidental or consequential damages, including lost profits arising from the use of these data. No warranty against infringement of any patent, copyright or trademark is made or implied.

End of Safety Data Sheet