


B3GNT1 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP13200b	WB, IHC, E	H	O43505 , NP_006867.1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB32886

Application Data:

Calculated MW: 47119 Da



B3GNT1 Antibody (C-term) (Cat. #AP13200b) western blot analysis in MDA-MB435 cell line lysates (35ug/lane). This demonstrates the B3GNT1 antibody detected the B3GNT1 protein (arrow).



B3GNT1 Antibody (C-term) (Cat. #AP13200b) immunohistochemistry analysis in formalin fixed and paraffin embedded human brain tissue followed by peroxidase conjugation of the secondary antibody and DAB staining. This data demonstrates the use of B3GNT1 Antibody (C-term) for immunohistochemistry. Clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
11041	B3GNT1

Other Names:

N-acetylglucosaminide beta-1,3-N-acetylglucosaminyltransferase;B3GNT1;B3GNT6

Target/Specificity:

This B3GNT1 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 365-394 amino acids from the C-terminal region of human B3GNT1.

Application Notes:

The suggested dilution is:
ELISA 1:1,000

Western blotting 1:100~500
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

B3GNT1 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

B3GNT1 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
