


TNFRSF10D Antibody (Center)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP9526c	WB, FC, E	H	Q9UBN6
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB24080

Application Data:

Calculated MW: 41823 Da



Western blot analysis of TNFRSF10D Antibody (Center) (Cat. #AP9526c) in HL-60 cell line lysates (35ug/lane). TNFRSF10D (arrow) was detected using the purified Pab.



TNFRSF10D Antibody (Center) (Cat. #AP9526c) flow cytometry analysis of Hela cells (bottom histogram) compared to a negative control cell (top histogram). FITC-conjugated goat-anti-rabbit secondary antibodies were used for the analysis.

Gene ID:	Gene Symbol:
8793	TNFRSF10D

Other Names:

CD_antigen=CD264; Flags: Precursor; TRAIL receptor with a truncated death domain; TNF-related apoptosis-inducing ligand receptor 4, TRAIL receptor 4; TRAIL-R4; Decoy receptor 2, DcR2; Tumor necrosis factor receptor superfamily member 10D; UNQ251/PRO288, TRUNDD, TRAILR4, DCR2, TNFRSF10D

Target/Specificity:

This TNFRSF10D antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 258~287 amino acids from the Central region of human TNFRSF10D.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Flow cytometry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

TNFRSF10D Antibody (Center) is for research use only and not for use in diagnostic or therapeutic procedures.
