

NSB526**eIF4G1 [p Ser1108] Antibody****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

eIF-4G [Ser1108]

Immunogen

Synthetic peptide (Human) derived from the region of human eIF-4G that contains serine 1108.

Recommended Dilutions

Western Blot 1:1,000

Buffer

PBS [pH 7.3] containing 1.0mg/ml BSA (IgG, protease free)

Uses

WB: Use at a concentration of 0.5 - 1.5 ug/ml. Predicted molecular weight: 200 kDa. Not tested in other applications. Optimal dilutions/concentrations should be determined by the end user.

Images

Peptide Competition: Extracts prepared from Hek293 cells were resolved on a 10% polyacrylamide gel and transferred to PVDF. Membranes were either treated with lambda (I) phosphatase (5) or untreated (1-4, 6), were blocked with a 3% non-fat ... See more at www.novusbio.com/NSB526



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

