


HTR3A Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP12192a	WB, E	H	NP_998786.2 , NP_000860.2 , NP_001155244.1 , P46098
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB32257
Application Data:		Calculated MW: 55280 Da	
		<p>HTR3A Antibody (N-term) (Cat. #AP12192a) western blot analysis in MDA-MB453, K562 cell line lysates (35ug/lane). This demonstrates the HTR3A antibody detected the HTR3A protein (arrow).</p>	
Gene ID:	Gene Symbol:		
3359	HTR3A		
Other Names:			
HTR3A, 5-hydroxytryptamine receptor 3A, 5HT3R; HTR3			
Target/Specificity:			
This HTR3A antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 37-66 amino acids from the N-terminal region of human HTR3A.			
Application Notes:			
The suggested dilution is: ELISA 1:1,000 Western blotting 1:100~500			
Format:			
Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.			

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

HTR3A Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
