


## LGALS4 Antibody (N-term)

### Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

<b>Catalog #</b>	<b>Applications:</b>	<b>Reactivity:</b>	<b>Accessions:</b>
AP12391a	WB, E	H	<a href="#">NP_006140.1</a> , <a href="#">P56470</a>
<b>Concentration:</b>	<b>Size:</b>	<b>Isotype:</b>	<b>Clone Name:</b>
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31354

#### Application Data: Calculated MW: 35941 Da



LGALS4 Antibody (N-term) (Cat. #AP12391a) western blot analysis in Jurkat cell line lysates (35ug/lane). This demonstrates the LGALS4 antibody detected the LGALS4 protein (arrow).

<b>Gene ID:</b>	<b>Gene Symbol:</b>
<a href="#">3960</a>	LGALS4

#### Other Names:

LGALS4;Galectin-4;

#### Target/Specificity:

This LGALS4 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 77-106 amino acids from the N-terminal region of human LGALS4.

#### Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

#### Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

#### Storage:

LGALS4 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20&deg;C.

---

**Precautions:**

LGALS4 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---