


FASTK Antibody (C-term)

Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP12464b	WB, IHC, E	H	NP_006703.1 , Q14296 , NP_148936.2
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB09593

Application Data:

Calculated MW: 61104 Da



Western blot analysis of FASTK (arrow) using rabbit polyclonal FASTK Antibody (C-term) (Cat. #AP12464b). 293 cell lysates (2 ug/lane) either nontransfected (Lane 1) or transiently transfected (Lane 2) with the FASTK gene.



FASTK Antibody (C-term) (Cat. #AP12464b) immunohistochemistry analysis in formalin fixed and paraffin embedded human liver tissue followed by peroxidase conjugation of the secondary antibody and DAB staining. This data demonstrates the use of FASTK Antibody (C-term) for immunohistochemistry. Clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
10922	FASTK

Other Names:

Fas-activated serine/threonine kinase;FASTK;

Target/Specificity:

This FASTK antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 394-424 amino acids from the C-terminal region of human FASTK.

Application Notes:

The suggested dilution is:

ELISA 1:1,000
Western blotting 1:50~100
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

Storage:

FASTK Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

FASTK Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
