


MYOGENIN Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP12509a	WB, E	H, M	P15173 , NP_002470.2
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31228

Application Data:

Calculated MW: 25037 Da



MYOGENIN Antibody (N-term) (Cat. #AP12509a) western blot analysis in ZR-75-1 cell line lysates (35ug/lane). This demonstrates the MYOGENIN antibody detected the MYOGENIN protein (arrow).



MYOGENIN Antibody (N-term) (Cat. #AP12509a) western blot analysis in mouse heart tissue lysates (35ug/lane). This demonstrates the MYOGENIN antibody detected the MYOGENIN protein (arrow).

Gene ID:	Gene Symbol:
4656	MYOG

Other Names:

Myogenin; MYOG; BHLHC3; MYF4

Target/Specificity:

This MYOGENIN antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 1-30 amino acids from the N-terminal region of human MYOGENIN.

Application Notes:

The suggested dilution is:
ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

MYOGENIN Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

MYOGENIN Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
