


MAP3K7IP3 Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP17071a	WB, E	H	Q8N5C8 , NP_690000.2
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB36935

Application Data:

Calculated MW: 78683 Da



MAP3K7IP3 Antibody (N-term) (Cat. #AP17071a) western blot analysis in HL-60 cell line lysates (35ug/lane). This demonstrates the MAP3K7IP3 antibody detected the MAP3K7IP3 protein (arrow).

Gene ID:	Gene Symbol:
257397	TAB3

Other Names:

TGF-beta-activated kinase 1 and MAP3K7-binding protein 3;TAB3;MAP3K7IP3

Target/Specificity:

This MAP3K7IP3 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 1-30 amino acids from the N-terminal region of human MAP3K7IP3.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

MAP3K7IP3 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

MAP3K7IP3 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
