


SNX2 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP16134b	WB, E	H	NP_003091.2 , O60749
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB35323

Application Data:

Calculated MW: 58471 Da



SNX2 Antibody (C-term) (Cat. #AP16134b) western blot analysis in A375 cell line lysates (35ug/lane). This demonstrates the SNX2 antibody detected the SNX2 protein (arrow).

Gene ID:	Gene Symbol:
6643	SNX2

Other Names:

Sorting nexin-2; SNX2;

Target/Specificity:

This SNX2 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 456-485 amino acids from the C-terminal region of human SNX2.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

SNX2 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

SNX2 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
