


NeuroD1 Antibody (C-term)

Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP2021b	WB, E	H, M	Q13562

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB2904

Application Data: Calculated MW: 39890 Da



Western blot analysis of anti-NeuroD1 Pab (Cat. #AP2021b) in mouse lung tissue lysate. NeuroD1 (arrow) was detected using purified Pab. Secondary HRP-anti-rabbit was used for signal visualization with chemiluminescence.



NeuroD1 Antibody (I333) (Cat. #AP2021b) western blot analysis in 293 cell line lysates (35ug/lane). This demonstrates the NeuroD1 antibody detected the NeuroD1 protein (arrow).

Gene ID:	Gene Symbol:
4760	NEUROD1

Other Names:

"Neurogenic differentiation factor 1, NeuroD"

Target/Specificity:

This NeuroD1 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 326~355 amino acids from the C-terminal region of human NeuroD1 protein.

Application Notes:

The suggested dilution will be:
ELISA 1:1,000

Western blotting 1:1,000

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein G column, eluted with high and low pH buffers and neutralized immediately, followed by dialysis against PBS.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

NeuroD1 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
