


## Mouse Mark3 Antibody (C-term)


### Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

<b>Catalog #</b>	<b>Applications:</b>	<b>Reactivity:</b>	<b>Accessions:</b>
AP14270b	WB, E	H, M	<a href="#">NP_067491.2</a> , <a href="#">NP_073712.2</a> , <a href="#">Q03141</a>
<b>Concentration:</b>	<b>Size:</b>	<b>Isotype:</b>	<b>Clone Name:</b>
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34835

**Application Data:**      **Calculated MW: 84390 Da**



Mouse Mark3 Antibody (C-term) (Cat. #AP14270b) western blot analysis in 293 cell line lysates (35ug/lane). This demonstrates the Mark3 antibody detected the Mark3 protein (arrow).



Mouse Mark3 Antibody (C-term) (Cat. #AP14270b) western blot analysis in mouse cerebellum tissue lysates (35ug/lane). This demonstrates the Mark3 antibody detected the Mark3 protein (arrow).

<b>Gene ID:</b>	<b>Gene Symbol:</b>
<a href="#">17169</a>	Mark3

**Other Names:**

MAP/microtubule affinity-regulating kinase 3; Mark3; Emk2; Mpk10

**Target/Specificity:**

This Mouse Mark3 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 607-636 amino acids from the C-terminal region of Mouse Mark3.

**Application Notes:**

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

---

**Format:**

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

---

**Storage:**

Mouse Mark3 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

---

**Precautions:**

Mouse Mark3 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---