


TNFSF14 Antibody (Center)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14595c	WB, E	H	NP_742011.2 , O43557 , NP_003798.2
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34583

Application Data:

Calculated MW: 26350 Da



TNFSF14 Antibody (Center) (Cat. #AP14595c) western blot analysis in A549 cell line lysates (35ug/lane). This demonstrates the TNFSF14 antibody detected the TNFSF14 protein (arrow).

Gene ID:	Gene Symbol:
8740	TNFSF14

Other Names:

Tumor necrosis factor ligand superfamily member 14;TNFSF14;HVEM; LIGHT

Target/Specificity:

This TNFSF14 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 65-94 amino acids from the Central region of human TNFSF14.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

TNFSF14 Antibody (Center) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

TNFSF14 Antibody (Center) is for research use only and not for use in diagnostic or therapeutic procedures.
