


Mouse Aurka Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14609a	WB, E	M	NP_035627.1 , P97477
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34736

Application Data: **Calculated MW: 44772 Da**



Mouse Aurka Antibody (N-term) (Cat. #AP14609a) western blot analysis in mouse NIH-3T3 cell line lysates (35ug/lane). This demonstrates the Aurka antibody detected the Aurka protein (arrow).

Gene ID: [20878](#)
Gene Symbol: Aurka

Other Names:

Serine/threonine-protein kinase 6; Aurka; Ark1; Ayk1; lak1; Stk6

Target/Specificity:

This Mouse Aurka antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 92-120 amino acids from the N-terminal region of Mouse Aurka.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Mouse Aurka Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term

storage, place the at -20°C.

Precautions:

Mouse Aurka Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
