


TAC2N Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP9427a	WB, IHC, E	H, M	Q8N9U0
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB24812

Application Data:

Calculated MW: 55257 Da



Western blot analysis of TAC2N Antibody (N-term) (Cat. #AP9427a) in mouse NIH-3T3 cell line lysates (35ug/lane). TAC2N (arrow) was detected using the purified Pab.



Formalin-fixed and paraffin-embedded human testis tissue reacted with TAC2N Antibody (N-term), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
123036	TC2N

Other Names:

Tandem C2 protein in nucleus, Tac2-N; Membrane targeting tandem C2 domain-containing protein 1; Tandem C2 domains nuclear protein, MTAC2D1, C14orf47, TC2N

Target/Specificity:

This TAC2N antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 9~39 amino acids from the N-terminal region of human TAC2N.

Application Notes:

The suggested dilution is:

ELISA 1:1,000
Western blotting 1:100~500
Immunohistochemistry 1:50~100

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

TAC2N Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
