


NOXA1 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP9567b	WB, E	H	Q86UR1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB24243

Application Data: Calculated MW: 50933 Da



Western blot analysis of NOXA1 Antibody (C-term) (Cat. #AP9567b) in MDA-MB435 cell line lysates (35ug/lane). NOXA1 (arrow) was detected using the purified Pab.

Gene ID:	Gene Symbol:
10811	NOXA1

Other Names:

Antigen NY-CO-31; NCF2-like protein; p51-nox; P67phox-like factor; NADPH oxidase activator 1, NOX activator 1; P51NOX, NOXA1

Target/Specificity:

This NOXA1 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 454~483 amino acids from the C-terminal region of human NOXA1.

Application Notes:

The suggested dilution is:
 ELISA 1:1,000
 Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

NOXA1 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
