


TLE1 Antibody (Center) (Ascites)

Mouse Monoclonal Antibody (Mab)

Catalog #	Applications:	Reactivity:	Accessions:
AM1982a	WB, E	H	Q04724 , NP_005068.2
Concentration:	Size:	Isotype:	Clone Name:
Crude ascites	0.1 ml	IgG1	381CT18.5.1

Application Data: Calculated MW: 83201 Da



TLE1 antibody (Center) (Cat. #AM1982a) western blot analysis in A549 cell line lysates (35ug/lane). This demonstrates the TLE1 antibody detected the TLE1 protein (arrow).

Gene ID:	Gene Symbol:
7088	TLE1

Other Names:

TLE1; Transducin-like enhancer protein 1;

Target/Specificity:

This TLE1 Monoclonal antibody is generated from mice immunized with a KLH conjugated synthetic peptide selected from the Central region of human TLE1.

Application Notes:

The suggested dilution is:

ELISA 1:1000

Western blotting 1:500~8000

Format:

Mouse monoclonal antibody supplied in crude ascites with 0.09% (W/V) sodium azide.

Storage:

TLE1 Antibody (Center) (Ascites) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

TLE1 Antibody (Center) (Ascites) is for research use only and not for use in diagnostic or therapeutic procedures.
