

according to the Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/02/2012

Version 1.1

SECTION 1. Identification

Product identifier

Product number 109925

Product name Potassium bromate solution for 1000 ml, c(KBrO₃) = 1/60 mol/l (0.1 N)

Titrisol®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses Reagent for analysis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-751-4321 | Monday to Friday, 9:00 AM to

4:00 PM Eastern Time (GMT-5)

e-mail: mm_sds@merckgroup.com

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Carcinogenicity, Category 1B, H350

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements
H350 May cause cancer.

Precautionary Statements

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109925 Version 1.1

Product name Potassium bromate solution for 1000 ml, c(KBrO₃) = 1/₅₀ mol/l (0.1 N) Titrisol®

P201 Obtain special instructions before use.

P308 + P313 IF exposed or concerned: Get medical advice/ attention.

Restricted to professional users.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature Aqueous solution

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Potassium bromate (>= 5 % - < 10 %)

7758-01-2

SECTION 4. First aid measures

Description of first-aid measures

General advice

First aider needs to protect himself.

Inhalation

After inhalation: fresh air. Call in physician.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Consult a

physician.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a

physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

gastric pain, Diarrhea, Nausea, Vomiting

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109925 Version 1.1

Product name Potassium bromate solution for 1000 ml, c(KBrO₃) = 1/₆₀ mol/l (0.1 N) Titrisol®

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

Protective equipment see section 8.

Environmental precautions

Do not let product enter drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up carefully with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Keep in a well-ventilated place. Keep locked up or in an area accessible only to qualified or authorized persons.

Storage temperature: no restrictions.

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109925 Version 1.1

Product name Potassium bromate solution for 1000 ml, c(KBrO₃) = 1/₅₀ mol/l (0.1 N) Titrisol®

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eve/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Recommended:

full contact:

Glove material: Nitrile rubber
Glove thickness: 0.11 mm
Break through time: > 480 min

splash contact:

Glove material: Nitrile rubber
Glove thickness: 0.11 mm
Break through time: > 480 min

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state liquid

Color colorless

Odor odorless

Odor Threshold No information available.

pH ca. 5.6

at 68 °F (20 °C)

Melting point No information available.

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109925 Version 1.1 Product name Potassium bromate solution for 1000 ml, $c(KBrO_3) = 1/60$ mol/l (0.1 N) Titrisol®

Boiling point No information available.

Flash point No information available.

Evaporation rate No information available.

Flammability (solid, gas) No information available.

Lower explosion limit No information available.

Upper explosion limit No information available.

Vapor pressure No information available.

Relative vapor density No information available.

Relative density ca. 1.04 g/cm³

at 68 °F (20 °C)

Water solubility at 68 °F (20 °C)

soluble

Partition coefficient: n-

octanol/water

No information available.

Autoignition temperature No information available.

Decomposition temperature No information available.

Viscosity, dynamic No information available.

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

Possibility of hazardous reactions

The generally known reaction partners of water.

Conditions to avoid

no information available

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109925 Version 1.1

Product name Potassium bromate solution for 1000 ml, c(KBrO₃) = 1/₆₀ mol/l (0.1 N) Titrisol®

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact

Acute oral toxicity

Symptoms: Nausea, Vomiting, gastric pain, Diarrhea

Acute toxicity estimate: > 2,000 mg/kg

Calculation method

Carcinogenicity

Carcinogenic in animal experiments.

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.

Further toxicological data:

Systemic effects:

Methemoglobinemia with headache, cardiac arrhythmia, drop in blood pressure, dyspnoea, and spasms, key symptom: cyanosis (blue coloration of the blood).

After a latency period:

Damage to: Kidney, Liver Further data:

Other dangerous properties can not be excluded.

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109925 Version 1.1

Product name Potassium bromate solution for 1000 ml, c(KBrO₃) = 1/₆₀ mol/l (0.1 N) Titrisol®

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Toxic by ingestion

Carcinogen

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

Chronic Health Hazard

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109925 Version 1.1

Product name Potassium bromate solution for 1000 ml, c(KBrO₃) = 1/60 mol/l (0.1 N) Titrisol®

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

US State Regulations

Massachusetts Right To Know

Ingredients

Potassium bromate

Pennsylvania Right To Know

Ingredients

water

Potassium bromate

New Jersey Right To Know

Ingredients

water

Potassium bromate

California Prop 65 Components

WARNING: this product contains a chemical known in the State of California to cause cancer.

Ingredients

Potassium bromate

Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL list.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H350 May cause cancer.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.