

NBP1-69283**UNC5C Antibody****Unit Size**

0.05 mg

Concentration

Lyoph

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB

Species

Human, Mouse, Rat, Bovine, Canine, Chicken, Porcine, Xenopus, Zebrafish

Host

Rabbit

Clonality

Polyclonal

Purity

Peptide affinity purified

Preservative

No Preservative

Immunogen

The immunogen for anti-UNC5C antibody: synthetic peptide directed towards the C terminal of human UNC5C (NP_003719). Peptide sequence
 WRMLAHKLNLDRLNYFATKSSPTGVILDLWEAQNFDPGNLSMLAAVLEE.

Recommended Dilutions

Western Blot 0.2-1 ug/ml

Buffer

Lyophilized from PBS & 2% Sucrose. Reconstitute with 50 ul of distilled water to a final concentration of 1 mg/ml in PBS buffer.

Images

Western Blot: UNC5C Antibody [NBP1-69283] - This Anti-UNC5C antibody was used in Western Blot of Jurkat tissue lysate at a concentration of 1ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

