

NBP2-11801**AMH Antibody (RM0288-8D29)****Unit Size**

0.1 mg

Concentration

Lyoph

Storage

Store at 4C. Do not freeze.

Applications

WB

Species

Mouse

Host

Rat

Clonality

Monoclonal

Isotype

IgG2

Purity

>95% pure by SDS-PAGE

Preservative

No Preservative

Immunogen

Mouse AMH

Recommended Dilutions

Western Blot

Buffer

Lyophilized in PBS

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP2-11801

Notes

Storage: Room temperature or 4 degree before antibody is re-suspended; -20 or -80 for longer period of storage after re-suspension.

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

