

NBP1-49981**TFIIB Antibody****Unit Size**

0.1 mg

Concentration

1 mg/ml

Storage

Store at 4°C. Do not freeze.

Applications

IP, PLA, WB (-)

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.09% Sodium Azide

Immunogen

The immunogen for this product maps to a region between residue 100 and 150 of human General Transcription Factor IIB using the numbering given in entry NP_001505.1 (GenelD 2959).

Recommended Dilutions

Immunoprecipitation 2 -5 ug/mg lysate
 Proximity Ligation Assay 1:1000 - 1:10000
 Western Blot (Negative)

Buffer


Tris-citrate/phosphate buffer, pH 7 to 8

Uses

This antibody works in 2 - 5 mcg/mg.

Images

Immunoprecipitation: TFIIB Antibody [NBP1-49981] - Detection of Human GTF2B/ TFIIB by Western Blot of Immunoprecipitates. Samples: Whole cell lysate (1 mg for IP, 20% of IP loaded) from Jurkat cells. Antibodies: Affinity purified rabbit ... See more at www.novusbio.com/NBP1-49981



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

