

NBP1-47259**ELF2 Antibody****Unit Size**

0.1 mg

Concentration

1 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB, IHC-P, IP (-)

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.09% Sodium Azide

Immunogen

The immunogen for this product maps to a region between residue 543 and 593 of human E74-like Factor 2 using the numbering given in entry EAX05123.1 (GeneID 1998).

Recommended Dilutions

Immunoprecipitation (Negative), Western Blot 1:2000 -1:10000, Immunohistochemistry-Paraffin

Buffer


Tris-citrate/phosphate buffer, pH 7 to 8

Uses

This product is useful in Western Blot.

Images

Immunohistochemistry-Paraffin: ELF2 Antibody [NBP1-47259] - Human ovarian carcinoma. Antibody used at a dilution of 1:1,000 (1ug/mg).



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

