

**NBP1-99615****TNF alpha Protein****Unit Size**

0.05 mg

**Concentration**

Lyoph

**Storage**

Store at -20C. Avoid freeze-thaw cycles.

**Species**

Mouse

**Purity**

&gt;95% pure by SDS-PAGE

**Specificity/Sensitivity**

Unit Definition:N/A

**Immunogen**

Source: E. coli.

Endotoxin Level: &lt;0.1 ng/ug

Activity (Specifications/test method):N/A

Biological activity:The EDSO as determined by the cytolysis of murine L929 cells in the presence of actinomycin D is < 0.1 ng/ml, corresponding to a specific activity of > 1 x 10<sup>7</sup>units/mg.

Results:N/A

Binding Capacity:N/A

**Buffer**

Steriled and lyophilized from 5 mM Tris, pH 8.0.

Reconstitute in H<sub>2</sub>O to a concentration of 0.1-1.0 . This solution can then be diluted into other aqueous buffers and stored at 4C for 1 week or -20C for future use.**Images**

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NBP1-99615](http://www.novusbio.com/NBP1-99615)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

