

NBP1-97735**Reticulon 1A/B Antibody (RNL-3)****Unit Size**

0.1 mg

Concentration

1 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, FLOW, ICC/IF, IHC, IHC-Fr

Species

Human, Primate, Rabbit

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

Affinity purified

Preservative

0.09% Sodium Azide

Immunogen

Clone RNL-3 is a mouse monoclonal IgG1 antibody derived by fusion of SP2/0-Ag14 mouse myeloma cells with spleen cells from a BALB/c mouse immunized with the small cell lung cancer cell line NCI-H82. RNL-3 recognizes an epitope located within the region of amino acids 421-589 of the neuro-endocrine specific protein Reticulon-1A (NSP-A), which is also present in the N-terminal part of Reticulon-1B (NSP-B).

Recommended Dilutions

Flow Cytometry 1:100 - 1:200, Immunohistochemistry-Frozen 1:100 - 1:200, Western Blot 1:100 - 1:500, Immunocytochemistry/Immunofluorescence, Immunohistochemistry

Buffer

PBS

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-97735

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

