

NBP1-22967**SMG7 Antibody****Unit Size**

0.1 ml

Concentration

0.2 mg/ml

Storage

Store at 4°C. Do not freeze.

Applications

WB, IP

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.09% Sodium Azide

Immunogen

The immunogen recognized by this antibody maps to a region between residue 1087 and 1137 of human suppressor with morphogenetic effect on genitalia protein 7 (ever shorter telomeres 1C) using the numbering given in entry NP_775179.1 (GeneID 9887).

Recommended Dilutions

Immunoprecipitation 5 -15 ug/mg lysate, Western Blot 1:2000 -1:10000

Buffer

Tris-buffered Saline and 0.1% BSA

Uses


This antibody is useful for western blot and immunoprecipitation.

References

Sakaki K, Yoshina S, Shen X, Han J, Desantis MR, Xiong M, Mitani S, Kaufman RJ. RNA surveillance is required for endoplasmic reticulum homeostasis. Proc Natl Acad Sci U S A;109(21):8079-84. 2012 May 22. [PMID: 22562797] (WB, Human)

Images

Western Blot: SMG7 Antibody [NBP1-22967] - Western Blot and Immunoprecipitation: SMG7 Antibody by Western Blot : Whole cell lysate from HeLa, 293T and mouse NIH3T3 cells. SMG7 was also immunoprecipitated by another rabbit anti-SMG7 antibody.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

