

NBP1-28012**CD69 Antibody (H1.2F3) [FITC]****Unit Size**

0.25 mg

Concentration

0.5 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

FLOW, IHC, IHC-Fr, IHC-P, In vitro, IP

Species

Mouse

Host

Armenian Hamster

Clonality

Monoclonal

Isotype

IgG Lambda

Conjugate

FITC

Purity

IgG purified

Preservative

Sodium Azide

Specificity/Sensitivity

Mouse CD69/Very Early Activation Antigen (VEA), Mr 85 kDa (unreduced)

Immunogen


Y245 mouse dendritic epidermal T cell line (1)

Recommended DilutionsFlow Cytometry < or =1 ug/10⁶ cells, Immunoprecipitation, Immunohistochemistry-Paraffin, Immunohistochemistry-Frozen, In vitro assay, Immunohistochemistry**Buffer**PBS/Na₃.**Uses**

Flow Cytometry, Immunoprecipitation, Immunohistochemistry-Paraffin, Immunohistochemistry-Frozen and In vitro assay

Images

Flow cytometry: CD69 Antibody (H1.2F3) [NBP1-28012] - less than or equal to 1 ug/10⁶ Fresh BALB/c spleen cells were activated by incubation for 20 hours with PMA + ionomycin, then stained with either hamster IgG-FITC (as an isotype contr... See more at www.novusbio.com/NBP1-28012

**Notes**

Protect conjugated forms from light.

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

